

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P696980

Luminaire Tested: **MRI-FEU4C-25-L950 F4X-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P696980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU4C-25-L950 F4X-M-X-LI
Description: 4 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 4LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2857.0 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P696980
CATALOG NUMBER: MRI-FEU4C-25-L950 F4X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P696980

CATALOG NUMBER: MRI-FEU4C-25-L950 F4X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	439250
5°	435070
10°	412269
15°	374299
20°	330754
25°	285951
30°	223513
35°	137078
40°	70356
45°	27955
50°	9078
55°	3127
60°	2678
65°	2151
70°	1329
75°	1756
80°	0
85°	0



TEST NUMBER: P696980
 CATALOG NUMBER: MRI-FEU4C-25-L950 F4X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.4	11.5
10°-20°	820.0	28.7
20°-30°	953.2	33.4
30°-40°	583.7	20.4
40°-50°	144.9	5.1
50°-60°	16.9	0.6
60°-70°	6.4	0.2
70°-80°	2.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2102.6	73.6
0°-40°	2686.4	94.0
0°-60°	2848.3	99.7
0°-90°	2857.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2857.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3575	
5°	3528	329
15°	2943	820
25°	2110	953
35°	914	584
45°	161	145
55°	15	17
65°	7	6
75°	4	2
85°	0	0
90°	0	



TEST NUMBER: P696980
CATALOG NUMBER: MRI-FEU4C-25-L950 F4X-M-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3575.4
2.5°	3571.7
5°	3527.9
7.5°	3432.8
10°	3304.8
12.5°	3136.7
15°	2942.9
17.5°	2734.6
20°	2529.9
22.5°	2325.1
25°	2109.5
27.5°	1860.8
30°	1575.6
32.5°	1243.0
35°	914.0
37.5°	643.4
40°	438.7
42.5°	274.1
45°	160.9
47.5°	91.4
50°	47.5
52.5°	22.0
55°	14.6
57.5°	10.9
60°	10.9
62.5°	7.4
65°	7.4
67.5°	3.7
70°	3.7
72.5°	3.7
75°	3.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)