

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P699254

Luminaire Tested: **MRI-FEU6C-40-L950 F6X-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P699254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-40-L950 F6X-N-X-H
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBNH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2681.0 lumens
Efficiency: N/A
Efficacy: 57.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P699254

CATALOG NUMBER: MRI-FEU6C-40-L950 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P699254

CATALOG NUMBER: MRI-FEU6C-40-L950 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		93
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		81
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		75
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		70
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		65
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		61
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		58
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		54
10	72	62	57	53	71	62	57	53	61	56	53		60	56	52		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188406
5°	183744
10°	169542
15°	150103
20°	130334
25°	111478
30°	91907
35°	60525
40°	32532
45°	14405
50°	5842
55°	4215
60°	2675
65°	1920
70°	1571
75°	1038
80°	1547
85°	0



TEST NUMBER: P699254
 CATALOG NUMBER: MRI-FEU6C-40-L950 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	309.1	11.5
10°-20°	737.0	27.5
20°-30°	844.3	31.5
30°-40°	567.3	21.2
40°-50°	162.1	6.0
50°-60°	39.7	1.5
60°-70°	15.1	0.6
70°-80°	5.8	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1890.4	70.5
0°-40°	2457.7	91.7
0°-60°	2659.4	99.2
0°-90°	2681.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2681.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3437	
5°	3339	309
15°	2645	737
25°	1843	844
35°	904	567
45°	186	162
55°	44	40
65°	15	15
75°	5	6
85°	0	1
90°	0	

TEST NUMBER: P699254

CATALOG NUMBER: MRI-FEU6C-40-L950 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3436.8
2.5°	3412.4
5°	3339.0
7.5°	3206.9
10°	3045.7
12.5°	2840.2
15°	2644.8
17.5°	2439.5
20°	2234.1
22.5°	2038.6
25°	1843.0
27.5°	1662.1
30°	1451.9
32.5°	1173.2
35°	904.4
37.5°	659.9
40°	454.6
42.5°	298.2
45°	185.8
47.5°	112.4
50°	68.5
52.5°	53.7
55°	44.1
57.5°	34.2
60°	24.4
62.5°	19.5
65°	14.8
67.5°	9.8
70°	9.8
72.5°	4.9
75°	4.9
77.5°	4.9
80°	4.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)