

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P699274

Luminaire Tested: **MRI-FEU6C-40-L950 F6X-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P699274
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-40-L950 F6X-W-X-H
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3772.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P699274
CATALOG NUMBER: MRI-FEU6C-40-L950 F6X-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P699274

CATALOG NUMBER: MRI-FEU6C-40-L950 F6X-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	112	109	106	103	110	107	104	101	103	100	98		99	97	95		91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		73
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		65
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		59
6	80	69	62	57	78	68	61	56	67	61	56		65	60	56		53
7	75	64	56	51	73	63	56	51	62	55	51		60	55	51		49
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		44
9	66	55	48	43	65	54	47	43	53	47	43		52	47	42		41
10	62	51	44	40	61	50	44	39	50	43	39		49	43	39		38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127534
5°	127493
10°	126512
15°	125665
20°	123747
25°	120920
30°	113853
35°	103041
40°	86040
45°	65929
50°	46694
55°	29437
60°	16611
65°	10779
70°	7036
75°	5168
80°	3094
85°	3082



TEST NUMBER: P699274
 CATALOG NUMBER: MRI-FEU6C-40-L950 F6X-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	5.8
10°-20°	623.5	16.5
20°-30°	914.2	24.2
30°-40°	951.5	25.2
40°-50°	658.3	17.5
50°-60°	286.6	7.6
60°-70°	87.9	2.3
70°-80°	26.3	0.7
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1757.4	46.6
0°-40°	2708.9	71.8
0°-60°	3653.8	96.9
0°-90°	3772.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3772.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2326	
5°	2317	220
15°	2214	624
25°	1999	914
35°	1540	951
45°	850	658
55°	308	287
65°	83	88
75°	24	26
85°	5	4
90°	0	



TEST NUMBER: P699274
CATALOG NUMBER: MRI-FEU6C-40-L950 F6X-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2326.4
2.5°	2331.4
5°	2316.8
7.5°	2297.3
10°	2272.7
12.5°	2248.2
15°	2214.2
17.5°	2170.1
20°	2121.2
22.5°	2067.5
25°	1999.1
27.5°	1911.1
30°	1798.6
32.5°	1681.3
35°	1539.7
37.5°	1383.3
40°	1202.3
42.5°	1021.5
45°	850.4
47.5°	689.1
50°	547.5
52.5°	415.5
55°	308.0
57.5°	220.0
60°	151.5
62.5°	112.4
65°	83.1
67.5°	63.6
70°	43.9
72.5°	34.3
75°	24.4
77.5°	14.6
80°	9.8
82.5°	4.9
85°	4.9
87.5°	0.0
90°	0.0

(END OF REPORT)