

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P697130

Luminaire Tested: **MRI-FEU4C-05-L940 F4X-N-X-H**

Issue Date: 08/03/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P697130  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-FEU4C-05-L940 F4X-N-X-H  
Description: 4 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 4LBNH TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 415.1 lumens  
Efficiency: N/A  
Efficacy: 57.6 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P697130  
CATALOG NUMBER: MRI-FEU4C-05-L940 F4X-N-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P697130

CATALOG NUMBER: MRI-FEU4C-05-L940 F4X-N-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 100 |
| 1   | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 |  | 101 | 99  | 98  |  | 93  |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 94  | 98  | 95  | 92  |  | 95  | 93  | 90  |  | 87  |
| 3   | 102 | 96  | 91  | 87  | 100 | 95  | 90  | 86  | 92  | 88  | 85  |  | 90  | 86  | 84  |  | 81  |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 75  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 73  | 81  | 76  | 73  |  | 80  | 75  | 72  |  | 70  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 72  | 68  | 76  | 72  | 68  |  | 75  | 71  | 67  |  | 65  |
| 7   | 83  | 74  | 68  | 64  | 82  | 73  | 68  | 64  | 72  | 67  | 63  |  | 71  | 66  | 63  |  | 61  |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 64  | 60  | 68  | 63  | 59  |  | 67  | 63  | 59  |  | 58  |
| 9   | 76  | 66  | 60  | 56  | 74  | 65  | 60  | 56  | 65  | 59  | 56  |  | 64  | 59  | 56  |  | 54  |
| 10  | 72  | 62  | 57  | 53  | 71  | 62  | 56  | 53  | 61  | 56  | 53  |  | 60  | 56  | 52  |  | 51  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 64019 |
| 5°  | 62586 |
| 10° | 57871 |
| 15° | 51931 |
| 20° | 45706 |
| 25° | 39338 |
| 30° | 31677 |
| 35° | 21087 |
| 40° | 10970 |
| 45° | 4969  |
| 50° | 2160  |
| 55° | 1456  |
| 60° | 934   |
| 65° | 669   |
| 70° | 539   |
| 75° | 380   |
| 80° | 0     |
| 85° | 0     |



TEST NUMBER: P697130  
 CATALOG NUMBER: MRI-FEU4C-05-L940 F4X-N-X-H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 47.0   | 11.3      |
| 10°-20°   | 114.0  | 27.5      |
| 20°-30°   | 132.4  | 31.9      |
| 30°-40°   | 87.7   | 21.1      |
| 40°-50°   | 24.6   | 5.9       |
| 50°-60°   | 6.2    | 1.5       |
| 60°-70°   | 2.3    | 0.6       |
| 70°-80°   | 0.8    | 0.2       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 293.4  | 70.7      |
| 0°-40°    | 381.1  | 91.8      |
| 0°-60°    | 411.9  | 99.2      |
| 0°-90°    | 415.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 415.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 521 |      |
| 5°  | 508 | 47   |
| 15° | 408 | 114  |
| 25° | 290 | 132  |
| 35° | 141 | 88   |
| 45° | 29  | 25   |
| 55° | 7   | 6    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P697130

CATALOG NUMBER: MRI-FEU4C-05-L940 F4X-N-X-H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 521.1 |
| 2.5°  | 518.8 |
| 5°    | 507.5 |
| 7.5°  | 487.9 |
| 10°   | 463.9 |
| 12.5° | 436.8 |
| 15°   | 408.3 |
| 17.5° | 380.4 |
| 20°   | 349.6 |
| 22.5° | 321.0 |
| 25°   | 290.2 |
| 27.5° | 260.9 |
| 30°   | 223.3 |
| 32.5° | 183.5 |
| 35°   | 140.6 |
| 37.5° | 100.8 |
| 40°   | 68.4  |
| 42.5° | 44.3  |
| 45°   | 28.6  |
| 47.5° | 17.3  |
| 50°   | 11.3  |
| 52.5° | 8.3   |
| 55°   | 6.8   |
| 57.5° | 5.3   |
| 60°   | 3.8   |
| 62.5° | 3.0   |
| 65°   | 2.3   |
| 67.5° | 1.5   |
| 70°   | 1.5   |
| 72.5° | 0.8   |
| 75°   | 0.8   |
| 77.5° | 0.8   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)