

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P697484

Luminaire Tested: **MRI-FEU6C-10-L950 F6X-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P697484
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-10-L950 F6X-W-X-LI
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 5000K, 90 CRI LEDS, 6LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1079.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P697484
CATALOG NUMBER: MRI-FEU6C-10-L950 F6X-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P697484

CATALOG NUMBER: MRI-FEU6C-10-L950 F6X-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	99		100	98	97		96
2	106	101	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	92	87	82	97	91	86	81	88	84	80		86	82	79		83
4	93	85	78	73	92	84	78	73	81	76	72		79	75	71		77
5	88	78	71	66	86	77	71	66	75	70	65		73	69	65		72
6	82	72	65	60	81	71	65	60	70	64	59		68	63	59		67
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	50	71	61	55	50	60	54	50		59	54	50		58
9	69	57	51	46	67	57	50	46	56	50	46		55	50	46		54
10	65	54	47	43	64	53	47	42	52	46	42		51	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36954
5°	37294
10°	38337
15°	39296
20°	39892
25°	39069
30°	36632
35°	32752
40°	26528
45°	17544
50°	8870
55°	3747
60°	1206
65°	480
70°	401
75°	254
80°	0
85°	0



TEST NUMBER: P697484
 CATALOG NUMBER: MRI-FEU6C-10-L950 F6X-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	6.0
10°-20°	195.5	18.1
20°-30°	294.6	27.3
30°-40°	301.6	28.0
40°-50°	175.7	16.3
50°-60°	40.4	3.7
60°-70°	5.0	0.5
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	555.1	51.4
0°-40°	856.7	79.4
0°-60°	1072.8	99.4
0°-90°	1079.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1079.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	674	
5°	678	65
15°	692	195
25°	646	295
35°	489	302
45°	226	176
55°	39	40
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P697484
CATALOG NUMBER: MRI-FEU6C-10-L950 F6X-W-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	674.1
2.5°	672.8
5°	677.7
7.5°	682.6
10°	688.7
12.5°	690.0
15°	692.4
17.5°	690.0
20°	683.8
22.5°	664.3
25°	645.9
27.5°	616.6
30°	578.7
32.5°	539.5
35°	489.4
37.5°	433.1
40°	370.7
42.5°	300.9
45°	226.3
47.5°	157.8
50°	104.0
52.5°	66.1
55°	39.2
57.5°	20.8
60°	11.0
62.5°	6.1
65°	3.7
67.5°	3.7
70°	2.5
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)