

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P698404

Luminaire Tested: **MRI-FEU6C-30-L927 F6X-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P698404
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-30-L927 F6X-M-X-LI
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2584.0 lumens
Efficiency: N/A
Efficacy: 81.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P698404
CATALOG NUMBER: MRI-FEU6C-30-L927 F6X-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P698404

CATALOG NUMBER: MRI-FEU6C-30-L927 F6X-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177277
5°	175588
10°	166385
15°	151062
20°	133484
25°	115404
30°	90210
35°	55319
40°	28396
45°	11280
50°	3667
55°	1262
60°	1085
65°	869
70°	529
75°	699
80°	0
85°	0



TEST NUMBER: P698404
 CATALOG NUMBER: MRI-FEU6C-30-L927 F6X-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	297.9	11.5
10°-20°	741.7	28.7
20°-30°	862.1	33.4
30°-40°	527.9	20.4
40°-50°	131.1	5.1
50°-60°	15.3	0.6
60°-70°	5.7	0.2
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1901.7	73.6
0°-40°	2429.7	94.0
0°-60°	2576.1	99.7
0°-90°	2584.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2584.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3234	
5°	3191	298
15°	2662	742
25°	1908	862
35°	827	528
45°	146	131
55°	13	15
65°	7	6
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P698404
CATALOG NUMBER: MRI-FEU6C-30-L927 F6X-M-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3233.8
2.5°	3230.4
5°	3190.8
7.5°	3104.8
10°	2989.0
12.5°	2837.0
15°	2661.7
17.5°	2473.3
20°	2288.1
22.5°	2102.9
25°	1907.9
27.5°	1683.0
30°	1425.1
32.5°	1124.2
35°	826.6
37.5°	581.9
40°	396.8
42.5°	247.9
45°	145.5
47.5°	82.7
50°	43.0
52.5°	19.9
55°	13.2
57.5°	9.9
60°	9.9
62.5°	6.7
65°	6.7
67.5°	3.3
70°	3.3
72.5°	3.3
75°	3.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)