

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P698894

Luminaire Tested: **MRI-FEU6C-35-L940 F6X-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P698894
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-35-L940 F6X-N-X-H
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBNH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2263.1 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P698894

CATALOG NUMBER: MRI-FEU6C-35-L940 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P698894

CATALOG NUMBER: MRI-FEU6C-35-L940 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159028
5°	155095
10°	143106
15°	126698
20°	110009
25°	94094
30°	77575
35°	51089
40°	27466
45°	12156
50°	4929
55°	3555
60°	2259
65°	1621
70°	1330
75°	890
80°	1326
85°	0



TEST NUMBER: P698894
 CATALOG NUMBER: MRI-FEU6C-35-L940 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	260.9	11.5
10°-20°	622.1	27.5
20°-30°	712.7	31.5
30°-40°	478.8	21.2
40°-50°	136.8	6.0
50°-60°	33.5	1.5
60°-70°	12.8	0.6
70°-80°	5.0	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1595.6	70.5
0°-40°	2074.5	91.7
0°-60°	2244.8	99.2
0°-90°	2263.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2263.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2901	
5°	2818	261
15°	2232	622
25°	1556	713
35°	763	479
45°	157	137
55°	37	33
65°	12	13
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P698894

CATALOG NUMBER: MRI-FEU6C-35-L940 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2900.9
2.5°	2880.3
5°	2818.4
7.5°	2706.9
10°	2570.8
12.5°	2397.4
15°	2232.4
17.5°	2059.2
20°	1885.7
22.5°	1720.8
25°	1555.6
27.5°	1403.0
30°	1225.5
32.5°	990.3
35°	763.4
37.5°	557.0
40°	383.8
42.5°	251.7
45°	156.8
47.5°	94.9
50°	57.8
52.5°	45.4
55°	37.2
57.5°	28.9
60°	20.6
62.5°	16.5
65°	12.5
67.5°	8.3
70°	8.3
72.5°	4.2
75°	4.2
77.5°	4.2
80°	4.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)