

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P699024

Luminaire Tested: **MRI-FEU6C-40-L927 F6X-N-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P699024
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-FEU6C-40-L927 F6X-N-X-LI
Description: 6 INCH FAIL-SAFE MRI LED DOWNLIGHT WITH 2700K, 90 CRI LEDS, 6LBNLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3146.0 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P699024
CATALOG NUMBER: MRI-FEU6C-40-L927 F6X-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P699024

CATALOG NUMBER: MRI-FEU6C-40-L927 F6X-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	86	86	85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	77	77	76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	73	73	72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	69	69	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	392660
5°	367207
10°	299482
15°	220382
20°	151902
25°	112773
30°	84709
35°	52822
40°	25641
45°	8799
50°	1151
55°	870
60°	504
65°	597
70°	737
75°	0
80°	0
85°	0



TEST NUMBER: P699024

CATALOG NUMBER: MRI-FEU6C-40-L927 F6X-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	595.5	18.9
10°-20°	1068.9	34.0
20°-30°	864.2	27.5
30°-40°	497.9	15.8
40°-50°	105.2	3.3
50°-60°	9.1	0.3
60°-70°	4.6	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2528.7	80.4
0°-40°	3026.6	96.2
0°-60°	3140.9	99.8
0°-90°	3146.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3146.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7163	
5°	6673	596
15°	3883	1069
25°	1864	864
35°	789	498
45°	114	105
55°	9	9
65°	5	5
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P699024

CATALOG NUMBER: MRI-FEU6C-40-L927 F6X-N-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7162.7
2.5°	7076.6
5°	6672.9
7.5°	6092.2
10°	5380.0
12.5°	4649.7
15°	3883.1
17.5°	3143.7
20°	2603.8
22.5°	2191.0
25°	1864.4
27.5°	1587.7
30°	1338.2
32.5°	1061.5
35°	789.3
37.5°	548.9
40°	358.3
42.5°	217.8
45°	113.5
47.5°	45.3
50°	13.5
52.5°	13.5
55°	9.1
57.5°	9.1
60°	4.6
62.5°	4.6
65°	4.6
67.5°	4.6
70°	4.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)