

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309284

Luminaire Tested: **24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-2700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309284
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-2700K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" ACRYLIC SHEET
Light Source: (168) 2700K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2256.0 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309284

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P309284

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	101	96	93	96	93	90		92	90	87		82
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		67
3	89	78	69	62	86	76	68	62	73	66	61		70	64	59		56
4	81	68	59	52	79	67	59	52	65	57	51		62	56	50		48
5	74	61	52	45	72	60	51	45	58	50	44		56	49	44		41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		36
7	63	50	41	34	62	49	40	34	47	39	34		46	39	34		31
8	59	45	36	30	57	44	36	30	43	36	30		42	35	30		28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	24		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	985	985	985
5°	986	982	986
10°	983	982	988
15°	977	980	989
20°	971	978	991
25°	959	973	993
30°	948	970	996
35°	932	965	998
40°	916	959	1007
45°	895	958	1023
50°	866	957	1050
55°	835	964	1088
60°	788	978	1136
65°	728	1001	1200
70°	635	1037	1278
75°	516	1090	1321
80°	380	1068	1068
85°	292	787	889



TEST NUMBER: P309284

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	3.1
10°-20°	199.1	8.8
20°-30°	303.1	13.4
30°-40°	368.1	16.3
40°-50°	388.9	17.2
50°-60°	366.9	16.3
60°-70°	305.1	13.5
70°-80°	200.7	8.9
80°-90°	54.7	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	571.6	25.3
0°-40°	939.7	41.7
0°-60°	1695.5	75.2
0°-90°	2256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2256.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	730	730	727	730	730	69
15°	702	703	704	710	710	198
25°	646	650	656	667	669	298
35°	568	574	588	603	607	355
45°	470	480	503	528	537	362
55°	356	371	411	450	464	317
65°	229	255	314	361	377	226
75°	99	144	210	248	254	107
85°	19	42	51	57	58	23
90°	0	0	0	0	0	



TEST NUMBER: P309284

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-HRP-CA125-W2A-U-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	732.0	732.0	732.0	732.0	732.0
2.5°	732.9	732.0	728.2	732.0	732.0
5°	730.1	730.1	727.2	730.1	730.1
7.5°	725.3	725.3	723.5	727.2	727.2
10°	719.7	719.7	718.7	723.5	723.5
12.5°	711.2	712.1	711.2	716.8	716.8
15°	701.7	702.7	703.6	710.2	710.2
17.5°	689.5	691.3	693.2	700.8	701.7
20°	678.1	679.1	682.8	691.3	692.3
22.5°	663.0	665.8	670.6	679.1	681.9
25°	646.0	649.8	655.5	666.8	668.7
27.5°	630.0	632.8	640.3	652.6	656.4
30°	610.1	614.8	624.3	636.6	641.3
32.5°	591.2	596.0	607.3	620.5	624.3
35°	567.6	574.2	587.5	602.6	607.3
37.5°	545.0	551.6	567.6	584.6	590.3
40°	521.3	528.9	545.9	565.7	573.3
42.5°	495.8	506.2	525.1	546.8	555.3
45°	470.3	479.8	503.4	528.0	537.4
47.5°	443.0	454.3	479.8	509.1	520.4
50°	413.7	427.8	457.1	489.2	501.5
52.5°	384.4	400.5	433.5	469.4	482.6
55°	356.1	371.2	410.8	449.6	463.7
57.5°	324.9	343.8	387.2	428.8	443.0
60°	292.8	313.6	363.6	407.1	422.2
62.5°	260.7	284.3	341.0	384.4	400.5
65°	228.6	255.0	314.5	360.8	376.8
67.5°	197.4	226.7	290.0	336.2	352.3
70°	161.5	198.3	263.5	308.8	324.9
72.5°	128.4	170.9	238.0	280.5	294.7
75°	99.2	144.5	209.7	248.4	254.1
77.5°	72.7	118.1	180.4	193.6	194.6
80°	49.1	94.4	137.9	136.0	137.9
82.5°	32.1	70.8	86.9	97.3	98.2
85°	18.9	41.6	51.0	56.7	57.6
87.5°	9.4	14.2	17.9	18.9	20.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)