

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309248

Luminaire Tested: **24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-2700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-2700K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125"
POLYCARB SHEET
Light Source: (336) 2700K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2188.0 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309248

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P309248

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	101	96	93	96	93	90		92	90	87		82
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		67
3	89	78	69	62	86	76	68	62	73	66	61		70	64	59		56
4	81	68	59	52	79	67	59	52	65	57	51		62	56	50		48
5	74	61	52	45	72	60	51	45	58	50	44		56	49	44		41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		36
7	63	50	41	34	62	49	40	34	47	39	34		46	39	34		31
8	59	45	36	30	57	44	36	30	43	36	30		42	35	30		28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	24		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	955	955	955
5°	956	953	956
10°	954	952	959
15°	948	951	959
20°	942	948	961
25°	930	944	963
30°	919	941	966
35°	904	936	967
40°	888	930	977
45°	868	929	992
50°	840	928	1018
55°	810	935	1055
60°	764	949	1102
65°	706	971	1164
70°	616	1006	1240
75°	500	1057	1281
80°	369	1036	1036
85°	283	764	863



TEST NUMBER: P309248

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.2	3.1
10°-20°	193.1	8.8
20°-30°	294.0	13.4
30°-40°	357.0	16.3
40°-50°	377.1	17.2
50°-60°	355.9	16.3
60°-70°	295.9	13.5
70°-80°	194.7	8.9
80°-90°	53.1	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.4	25.3
0°-40°	911.3	41.7
0°-60°	1644.4	75.2
0°-90°	2188.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2188.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	710	710	710	710	710	
5°	708	708	705	708	708	67
15°	681	682	682	689	689	192
25°	626	630	636	647	648	289
35°	550	557	570	584	589	345
45°	456	465	488	512	521	351
55°	345	360	398	436	450	308
65°	222	247	305	350	366	219
75°	96	140	203	241	246	104
85°	18	40	50	55	56	22
90°	0	0	0	0	0	



TEST NUMBER: P309248

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-HRP-CP125-W2A-U-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	709.9	709.9	709.9	709.9	709.9
2.5°	710.8	709.9	706.2	709.9	709.9
5°	708.1	708.1	705.3	708.1	708.1
7.5°	703.5	703.5	701.7	705.3	705.3
10°	698.0	698.0	697.1	701.7	701.7
12.5°	689.7	690.7	689.7	695.2	695.2
15°	680.6	681.5	682.4	688.8	688.8
17.5°	668.7	670.5	672.3	679.7	680.6
20°	657.7	658.6	662.3	670.5	671.4
22.5°	643.0	645.8	650.4	658.6	661.4
25°	626.5	630.2	635.7	646.7	648.5
27.5°	611.0	613.7	621.0	633.0	636.6
30°	591.7	596.3	605.5	617.4	622.0
32.5°	573.4	578.0	589.0	601.8	605.5
35°	550.5	556.9	569.8	584.4	589.0
37.5°	528.5	534.9	550.5	567.0	572.5
40°	505.6	513.0	529.4	548.7	556.0
42.5°	480.9	491.0	509.3	530.4	538.6
45°	456.2	465.3	488.2	512.0	521.2
47.5°	429.6	440.6	465.3	493.7	504.7
50°	401.2	414.9	443.3	474.5	486.4
52.5°	372.8	388.4	420.4	455.3	468.1
55°	345.3	360.0	398.5	436.0	449.8
57.5°	315.1	333.4	375.6	415.9	429.6
60°	284.0	304.1	352.7	394.8	409.5
62.5°	252.8	275.7	330.7	372.8	388.4
65°	221.7	247.3	305.0	349.9	365.5
67.5°	191.4	219.8	281.2	326.1	341.7
70°	156.6	192.4	255.6	299.5	315.1
72.5°	124.6	165.8	230.8	272.1	285.8
75°	96.2	140.1	203.4	240.9	246.4
77.5°	70.5	114.5	175.0	187.8	188.7
80°	47.6	91.6	133.7	131.9	133.7
82.5°	31.1	68.7	84.3	94.3	95.3
85°	18.3	40.3	49.5	55.0	55.9
87.5°	9.2	13.7	17.4	18.3	20.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)