

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309331

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-HRP-CA125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L82765-HRP-CA125-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2749.0 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 30.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309331

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-HRP-CA125-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P309331

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-HRP-CA125-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	101	96	93	96	93	90		92	90	87		82
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		67
3	89	78	69	62	86	76	68	62	73	66	61		70	64	59		56
4	81	68	59	52	79	67	59	52	65	57	51		62	56	50		48
5	74	61	52	45	72	60	51	45	58	50	44		56	49	44		41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		36
7	63	50	41	34	62	49	40	34	47	39	34		46	39	34		31
8	59	45	36	30	57	44	36	30	43	36	30		42	35	30		28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	24		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1200	1200	1200
5°	1202	1197	1202
10°	1198	1197	1204
15°	1191	1194	1205
20°	1183	1191	1208
25°	1169	1186	1210
30°	1155	1182	1214
35°	1136	1176	1215
40°	1116	1168	1227
45°	1091	1167	1246
50°	1055	1166	1279
55°	1018	1174	1326
60°	960	1192	1384
65°	887	1220	1462
70°	774	1263	1557
75°	628	1328	1609
80°	463	1302	1302
85°	355	959	1084



TEST NUMBER: P309331

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-HRP-CA125-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.5	3.1
10°-20°	242.6	8.8
20°-30°	369.4	13.4
30°-40°	448.5	16.3
40°-50°	473.8	17.2
50°-60°	447.1	16.3
60°-70°	371.8	13.5
70°-80°	244.6	8.9
80°-90°	66.7	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	696.5	25.3
0°-40°	1145.0	41.7
0°-60°	2066.0	75.2
0°-90°	2749.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2749.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	892	892	892	892	892	
5°	890	890	886	890	890	84
15°	855	856	857	865	865	241
25°	787	792	799	812	815	363
35°	692	700	716	734	740	433
45°	573	585	613	643	655	441
55°	434	452	501	548	565	386
65°	278	311	383	440	459	275
75°	121	176	256	303	310	130
85°	23	51	62	69	70	28
90°	0	0	0	0	0	



TEST NUMBER: P309331

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-HRP-CA125-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.9	891.9	891.9	891.9	891.9
2.5°	893.1	891.9	887.3	891.9	891.9
5°	889.6	889.6	886.2	889.6	889.6
7.5°	883.9	883.9	881.6	886.2	886.2
10°	877.0	877.0	875.8	881.6	881.6
12.5°	866.6	867.7	866.6	873.5	873.5
15°	855.1	856.2	857.4	865.4	865.4
17.5°	840.1	842.4	844.7	853.9	855.1
20°	826.3	827.5	832.1	842.4	843.6
22.5°	807.9	811.4	817.1	827.5	830.9
25°	787.2	791.8	798.7	812.5	814.8
27.5°	767.6	771.1	780.3	795.2	799.8
30°	743.5	749.2	760.7	775.7	781.4
32.5°	720.4	726.2	740.0	756.1	760.7
35°	691.7	699.7	715.8	734.2	740.0
37.5°	664.0	672.1	691.7	712.4	719.3
40°	635.3	644.5	665.2	689.4	698.6
42.5°	604.2	616.9	639.9	666.3	676.7
45°	573.1	584.6	613.4	643.3	654.8
47.5°	539.8	553.6	584.6	620.3	634.1
50°	504.1	521.3	557.0	596.1	611.1
52.5°	468.4	488.0	528.2	572.0	588.1
55°	433.9	452.3	500.6	547.8	565.1
57.5°	395.9	418.9	471.9	522.5	539.8
60°	356.8	382.1	443.1	496.0	514.4
62.5°	317.6	346.4	415.5	468.4	488.0
65°	278.5	310.7	383.2	439.6	459.2
67.5°	240.5	276.2	353.3	409.7	429.3
70°	196.8	241.7	321.1	376.3	395.9
72.5°	156.5	208.3	290.0	341.8	359.1
75°	120.8	176.1	255.5	302.7	309.6
77.5°	88.6	143.9	219.8	235.9	237.1
80°	59.8	115.1	168.0	165.7	168.0
82.5°	39.1	86.3	105.9	118.5	119.7
85°	23.0	50.6	62.1	69.1	70.2
87.5°	11.5	17.3	21.9	23.0	25.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)