

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310017

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-RDP-CP125-W2A-U-4500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310017
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L82765-RDP-CP125-W2A-U-4500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" POLYCARB SHEET
Light Source: (336) 4500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2486.0 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 31
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310017

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP125-W2A-U-4500K

Luminous Intensity Polar Plot





TEST NUMBER: P310017

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP125-W2A-U-4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	100	96	92	96	93	89		92	89	87		82
2	97	89	81	75	95	87	80	74	83	77	72		80	75	71		67
3	88	77	68	62	86	76	67	61	72	66	60		70	64	59		56
4	81	68	59	52	78	67	58	51	64	57	51		62	55	50		47
5	74	60	51	44	72	59	51	44	57	49	43		55	48	43		40
6	68	54	45	38	66	53	45	38	51	44	38		50	43	37		35
7	63	49	40	34	61	48	40	34	47	39	33		45	38	33		31
8	59	45	36	30	57	44	36	30	43	35	30		41	34	29		27
9	55	41	33	27	53	40	32	27	39	32	27		38	31	26		24
10	51	38	30	24	50	37	29	24	36	29	24		35	29	24		22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1052	1052	1052
5°	1056	1049	1054
10°	1053	1050	1055
15°	1051	1049	1056
20°	1044	1049	1059
25°	1040	1051	1062
30°	1031	1048	1065
35°	1021	1045	1069
40°	1009	1044	1083
45°	993	1044	1107
50°	970	1051	1141
55°	946	1067	1192
60°	906	1089	1257
65°	848	1127	1335
70°	771	1179	1436
75°	654	1243	1500
80°	516	1251	1213
85°	381	953	1067



TEST NUMBER: P310017

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP125-W2A-U-4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.2	3.0
10°-20°	213.4	8.6
20°-30°	326.4	13.1
30°-40°	399.0	16.0
40°-50°	425.2	17.1
50°-60°	406.6	16.4
60°-70°	344.4	13.9
70°-80°	231.5	9.3
80°-90°	65.3	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	614.0	24.7
0°-40°	1013.0	40.7
0°-60°	1844.8	74.2
0°-90°	2486.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2486.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	782	782	782	782	782	
5°	782	780	777	780	780	74
15°	755	755	753	760	758	213
25°	700	703	708	714	715	323
35°	622	626	636	649	651	389
45°	522	530	549	572	582	402
55°	403	418	455	491	508	359
65°	266	294	354	401	419	264
75°	126	171	239	280	288	135
85°	25	51	62	67	69	31
90°	0	0	0	0	0	



TEST NUMBER: P310017

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP125-W2A-U-4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	781.8	781.8	781.8	781.8	781.8
2.5°	783.0	783.0	779.3	781.8	781.8
5°	781.8	780.5	776.8	780.5	780.5
7.5°	778.1	776.8	774.4	778.1	776.8
10°	770.7	770.7	768.2	771.9	771.9
12.5°	764.5	763.3	762.0	767.0	765.7
15°	754.6	754.6	753.4	759.6	758.3
17.5°	742.3	743.6	744.8	749.7	750.9
20°	728.8	731.2	732.5	739.9	739.9
22.5°	716.4	717.7	720.1	727.5	727.5
25°	700.4	702.9	707.8	714.0	715.2
27.5°	684.4	685.6	691.8	700.4	701.6
30°	663.4	667.1	674.5	684.4	685.6
32.5°	644.9	648.6	657.2	667.1	669.6
35°	621.5	626.4	636.3	648.6	651.1
37.5°	600.5	604.2	616.5	630.1	633.8
40°	574.6	582.0	594.3	610.4	616.5
42.5°	548.7	556.1	570.9	591.9	599.3
45°	521.6	530.2	548.7	572.2	582.0
47.5°	494.5	504.3	525.3	552.4	563.5
50°	463.6	476.0	501.9	532.7	545.0
52.5°	434.0	448.8	477.2	511.7	527.8
55°	403.2	418.0	455.0	490.8	508.0
57.5°	368.7	388.4	429.1	469.8	488.3
60°	336.6	355.1	404.5	448.8	467.3
62.5°	302.1	326.8	379.8	426.6	445.1
65°	266.3	293.5	353.9	400.8	419.2
67.5°	234.3	263.9	328.0	374.9	393.4
70°	196.1	233.1	299.6	346.5	365.0
72.5°	160.3	201.0	270.0	315.7	332.9
75°	125.8	171.4	239.2	279.9	288.5
77.5°	93.7	141.8	207.2	224.4	218.3
80°	66.6	113.4	161.5	152.9	156.6
82.5°	43.2	86.3	99.9	113.4	117.1
85°	24.7	50.6	61.7	66.6	69.1
87.5°	11.1	18.5	24.7	24.7	23.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)