

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310039

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-RDP-CP250-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L82765-RDP-CP250-W2A-U-6500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.250" POLYCARB SHEET
Light Source: (336) 6500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2429.0 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 31.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310039

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP250-W2A-U-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P310039

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP250-W2A-U-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	100	96	92	96	93	89		92	89	87		82
2	97	89	81	75	95	87	80	74	83	77	72		80	75	71		67
3	88	77	68	62	86	76	67	61	72	66	60		70	64	59		56
4	81	68	59	52	78	67	58	51	64	57	51		62	55	50		47
5	74	60	51	44	72	59	51	44	57	49	43		55	48	43		40
6	68	54	45	38	66	53	45	38	51	44	38		50	43	37		35
7	63	49	40	34	61	48	40	34	47	39	33		45	38	33		31
8	59	45	36	30	57	44	36	30	43	35	30		41	34	29		27
9	55	41	33	27	53	40	32	27	39	32	27		38	31	26		24
10	51	38	30	24	50	37	29	24	36	29	24		35	29	24		22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1028	1028	1028
5°	1032	1025	1030
10°	1029	1026	1030
15°	1027	1025	1032
20°	1019	1025	1035
25°	1016	1027	1037
30°	1007	1024	1041
35°	997	1021	1045
40°	986	1020	1058
45°	970	1020	1082
50°	948	1027	1115
55°	924	1043	1164
60°	885	1063	1229
65°	828	1101	1304
70°	754	1152	1403
75°	639	1215	1465
80°	504	1223	1185
85°	372	929	1042



TEST NUMBER: P310039

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP250-W2A-U-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.5	3.0
10°-20°	208.5	8.6
20°-30°	318.9	13.1
30°-40°	389.8	16.0
40°-50°	415.5	17.1
50°-60°	397.3	16.4
60°-70°	336.5	13.9
70°-80°	226.2	9.3
80°-90°	63.8	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.9	24.7
0°-40°	989.7	40.7
0°-60°	1802.5	74.2
0°-90°	2429.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2429.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	764	764	764	764	764	
5°	764	763	759	763	763	73
15°	737	737	736	742	741	208
25°	684	687	692	698	699	315
35°	607	612	622	634	636	380
45°	510	518	536	559	569	393
55°	394	408	445	480	496	351
65°	260	287	346	392	410	258
75°	123	168	234	274	282	132
85°	24	49	60	65	68	30
90°	0	0	0	0	0	



TEST NUMBER: P310039

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-RDP-CP250-W2A-U-6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	763.9	763.9	763.9	763.9	763.9
2.5°	765.1	765.1	761.4	763.9	763.9
5°	763.9	762.6	759.0	762.6	762.6
7.5°	760.2	759.0	756.6	760.2	759.0
10°	753.0	753.0	750.6	754.2	754.2
12.5°	747.0	745.8	744.6	749.4	748.2
15°	737.3	737.3	736.1	742.2	741.0
17.5°	725.3	726.5	727.7	732.5	733.7
20°	712.0	714.5	715.7	722.9	722.9
22.5°	700.0	701.2	703.6	710.8	710.8
25°	684.3	686.7	691.6	697.6	698.8
27.5°	668.7	669.9	675.9	684.3	685.5
30°	648.2	651.8	659.0	668.7	669.9
32.5°	630.1	633.7	642.2	651.8	654.2
35°	607.2	612.0	621.7	633.7	636.1
37.5°	586.7	590.4	602.4	615.7	619.3
40°	561.4	568.7	580.7	596.4	602.4
42.5°	536.1	543.4	557.8	578.3	585.5
45°	509.6	518.1	536.1	559.0	568.7
47.5°	483.1	492.8	513.3	539.8	550.6
50°	453.0	465.1	490.4	520.5	532.5
52.5°	424.1	438.6	466.3	500.0	515.7
55°	394.0	408.4	444.6	479.5	496.4
57.5°	360.2	379.5	419.3	459.0	477.1
60°	328.9	347.0	395.2	438.6	456.6
62.5°	295.2	319.3	371.1	416.9	434.9
65°	260.2	286.7	345.8	391.6	409.6
67.5°	228.9	257.8	320.5	366.3	384.3
70°	191.6	227.7	292.8	338.6	356.6
72.5°	156.6	196.4	263.9	308.4	325.3
75°	122.9	167.5	233.7	273.5	281.9
77.5°	91.6	138.6	202.4	219.3	213.3
80°	65.1	110.8	157.8	149.4	153.0
82.5°	42.2	84.3	97.6	110.8	114.5
85°	24.1	49.4	60.2	65.1	67.5
87.5°	10.8	18.1	24.1	24.1	22.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)