

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309519

Luminaire Tested: **24FCZ2-50HE-UNV-L82765-HRP-CP125-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309519
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-50HE-UNV-L82765-HRP-CP125-W2A-U-3000K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125"
POLYCARB SHEET
Light Source: (336) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3215.0 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 38.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309519

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-HRP-CP125-W2A-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P309519

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-HRP-CP125-W2A-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	101	96	93	96	93	90		92	90	87		82
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		67
3	89	78	69	62	86	76	68	62	73	66	61		70	64	59		56
4	81	68	59	52	79	67	59	52	65	57	51		62	56	50		48
5	74	61	52	45	72	60	51	45	58	50	44		56	49	44		41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		36
7	63	50	41	34	62	49	40	34	47	39	34		46	39	34		31
8	59	45	36	30	57	44	36	30	43	36	30		42	35	30		28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	24		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1403	1403	1403
5°	1405	1400	1405
10°	1401	1399	1409
15°	1393	1397	1410
20°	1384	1393	1413
25°	1367	1387	1415
30°	1351	1382	1420
35°	1329	1375	1421
40°	1305	1366	1435
45°	1275	1365	1457
50°	1234	1364	1496
55°	1190	1373	1550
60°	1123	1394	1619
65°	1037	1427	1710
70°	906	1477	1821
75°	735	1553	1882
80°	542	1523	1523
85°	415	1122	1267



TEST NUMBER: P309519

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-HRP-CP125-W2A-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	3.1
10°-20°	283.8	8.8
20°-30°	432.0	13.4
30°-40°	524.5	16.3
40°-50°	554.2	17.2
50°-60°	522.9	16.3
60°-70°	434.8	13.5
70°-80°	286.0	8.9
80°-90°	78.0	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.6	25.3
0°-40°	1339.1	41.7
0°-60°	2416.2	75.2
0°-90°	3215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3215.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1043	1043	1043	1043	1043	
5°	1040	1040	1036	1040	1040	99
15°	1000	1001	1003	1012	1012	282
25°	921	926	934	950	953	425
35°	809	818	837	859	865	506
45°	670	684	717	752	766	516
55°	507	529	586	641	661	452
65°	326	363	448	514	537	322
75°	141	206	299	354	362	152
85°	27	59	73	81	82	33
90°	0	0	0	0	0	



TEST NUMBER: P309519

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-HRP-CP125-W2A-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1043.1	1043.1	1043.1	1043.1	1043.1
2.5°	1044.5	1043.1	1037.7	1043.1	1043.1
5°	1040.4	1040.4	1036.4	1040.4	1040.4
7.5°	1033.7	1033.7	1031.0	1036.4	1036.4
10°	1025.6	1025.6	1024.3	1031.0	1031.0
12.5°	1013.5	1014.8	1013.5	1021.6	1021.6
15°	1000.0	1001.4	1002.7	1012.2	1012.2
17.5°	982.5	985.2	987.9	998.7	1000.0
20°	966.4	967.7	973.1	985.2	986.6
22.5°	944.9	948.9	955.6	967.7	971.8
25°	920.6	926.0	934.1	950.2	952.9
27.5°	897.7	901.8	912.6	930.0	935.4
30°	869.5	876.2	889.7	907.2	913.9
32.5°	842.6	849.3	865.4	884.3	889.7
35°	808.9	818.3	837.2	858.7	865.4
37.5°	776.6	786.0	808.9	833.1	841.2
40°	743.0	753.7	778.0	806.2	817.0
42.5°	706.6	721.4	748.3	779.3	791.4
45°	670.3	683.7	717.4	752.4	765.8
47.5°	631.2	647.4	683.7	725.5	741.6
50°	589.5	609.7	651.4	697.2	714.7
52.5°	547.8	570.7	617.8	668.9	687.8
55°	507.4	529.0	585.5	640.7	660.9
57.5°	463.0	489.9	551.8	611.1	631.2
60°	417.2	446.9	518.2	580.1	601.6
62.5°	371.5	405.1	485.9	547.8	570.7
65°	325.7	363.4	448.2	514.2	537.0
67.5°	281.3	323.0	413.2	479.2	502.0
70°	230.2	282.6	375.5	440.1	463.0
72.5°	183.0	243.6	339.2	399.7	419.9
75°	141.3	205.9	298.8	354.0	362.1
77.5°	103.6	168.2	257.1	275.9	277.3
80°	70.0	134.6	196.5	193.8	196.5
82.5°	45.8	100.9	123.8	138.6	140.0
85°	26.9	59.2	72.7	80.8	82.1
87.5°	13.5	20.2	25.6	26.9	29.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)