

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309745

Luminaire Tested: **24FCZ2-70HE-UNV-L82765-HRP-CP125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-20)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-70HE-UNV-L82765-HRP-CP125-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, HIGH EFFICIENCY RND PERF. LENS, 0.125"
POLYCARB SHEET
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4667.0 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.3 / 1.4
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 58
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309745

CATALOG NUMBER: 24FCZ2-70HE-UNV-L82765-HRP-CP125-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P309745

CATALOG NUMBER: 24FCZ2-70HE-UNV-L82765-HRP-CP125-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	101	96	93	96	93	90		92	90	87		82
2	98	89	82	76	95	87	80	75	83	78	73		80	75	71		67
3	89	78	69	62	86	76	68	62	73	66	61		70	64	59		56
4	81	68	59	52	79	67	59	52	65	57	51		62	56	50		48
5	74	61	52	45	72	60	51	45	58	50	44		56	49	44		41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		36
7	63	50	41	34	62	49	40	34	47	39	34		46	39	34		31
8	59	45	36	30	57	44	36	30	43	36	30		42	35	30		28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	24		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2037	2037	2037
5°	2040	2032	2040
10°	2034	2031	2045
15°	2022	2028	2047
20°	2009	2023	2051
25°	1984	2013	2054
30°	1961	2007	2061
35°	1929	1996	2064
40°	1894	1984	2083
45°	1851	1982	2115
50°	1791	1979	2172
55°	1728	1994	2250
60°	1630	2024	2350
65°	1505	2071	2482
70°	1314	2144	2644
75°	1067	2255	2732
80°	787	2211	2211
85°	604	1629	1840



TEST NUMBER: P309745

CATALOG NUMBER: 24FCZ2-70HE-UNV-L82765-HRP-CP125-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.4	3.1
10°-20°	411.9	8.8
20°-30°	627.1	13.4
30°-40°	761.4	16.3
40°-50°	804.4	17.2
50°-60°	759.1	16.3
60°-70°	631.2	13.5
70°-80°	415.2	8.9
80°-90°	113.2	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1182.4	25.3
0°-40°	1943.9	41.7
0°-60°	3507.4	75.2
0°-90°	4667.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4667.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1514	1514	1514	1514	1514	
5°	1510	1510	1504	1510	1510	143
15°	1452	1454	1456	1469	1469	409
25°	1336	1344	1356	1379	1383	616
35°	1174	1188	1215	1246	1256	735
45°	973	992	1041	1092	1112	749
55°	737	768	850	930	959	656
65°	473	528	651	746	780	467
75°	205	299	434	514	526	221
85°	39	86	106	117	119	48
90°	0	0	0	0	0	



TEST NUMBER: P309745

CATALOG NUMBER: 24FCZ2-70HE-UNV-L82765-HRP-CP125-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1514.2	1514.2	1514.2	1514.2	1514.2
2.5°	1516.2	1514.2	1506.4	1514.2	1514.2
5°	1510.3	1510.3	1504.4	1510.3	1510.3
7.5°	1500.5	1500.5	1496.6	1504.4	1504.4
10°	1488.8	1488.8	1486.9	1496.6	1496.6
12.5°	1471.2	1473.2	1471.2	1483.0	1483.0
15°	1451.7	1453.6	1455.6	1469.3	1469.3
17.5°	1426.3	1430.2	1434.1	1449.7	1451.7
20°	1402.8	1404.8	1412.6	1430.2	1432.2
22.5°	1371.6	1377.4	1387.2	1404.8	1410.7
25°	1336.4	1344.2	1356.0	1379.4	1383.3
27.5°	1303.2	1309.1	1324.7	1350.1	1357.9
30°	1262.2	1271.9	1291.5	1316.9	1326.6
32.5°	1223.1	1232.9	1256.3	1283.7	1291.5
35°	1174.2	1187.9	1215.3	1246.5	1256.3
37.5°	1127.4	1141.0	1174.2	1209.4	1221.1
40°	1078.5	1094.1	1129.3	1170.3	1186.0
42.5°	1025.8	1047.2	1086.3	1131.3	1148.8
45°	973.0	992.5	1041.4	1092.2	1111.7
47.5°	916.3	939.8	992.5	1053.1	1076.6
50°	855.8	885.1	945.6	1012.1	1037.5
52.5°	795.2	828.4	896.8	971.0	998.4
55°	736.6	767.9	849.9	930.0	959.3
57.5°	672.1	711.2	801.1	887.0	916.3
60°	605.7	648.7	752.2	842.1	873.4
62.5°	539.3	588.1	705.3	795.2	828.4
65°	472.8	527.5	650.6	746.4	779.6
67.5°	408.3	468.9	599.8	695.6	728.8
70°	334.1	410.3	545.1	638.9	672.1
72.5°	265.7	353.6	492.4	580.3	609.6
75°	205.2	298.9	433.7	513.9	525.6
77.5°	150.4	244.2	373.2	400.5	402.5
80°	101.6	195.4	285.3	281.4	285.3
82.5°	66.4	146.5	179.8	201.2	203.2
85°	39.1	86.0	105.5	117.2	119.2
87.5°	19.5	29.3	37.1	39.1	43.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)