

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310509

Luminaire Tested: **24FCZ2-30HE-UNV-L82765-CP125-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310509
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-30HE-UNV-L82765-CP125-W2A-U-3000K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.125" POLYCARB SHEET
Light Source: (336) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2589.0 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 21
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310509

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-CP125-W2A-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P310509

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-CP125-W2A-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82		
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67		
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56		
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47		
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41		
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36		
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31		
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28		
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25		
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1149	1149	1149
5°	1151	1144	1151
10°	1144	1141	1150
15°	1134	1137	1151
20°	1120	1129	1150
25°	1103	1121	1149
30°	1082	1112	1148
35°	1061	1101	1148
40°	1036	1092	1156
45°	1012	1085	1165
50°	982	1082	1183
55°	957	1084	1207
60°	920	1093	1248
65°	878	1105	1294
70°	831	1139	1365
75°	741	1188	1491
80°	632	1258	1524
85°	451	1246	1459



TEST NUMBER: P310509

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-CP125-W2A-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.8	3.1
10°-20°	231.1	8.9
20°-30°	349.0	13.5
30°-40°	420.6	16.2
40°-50°	441.6	17.1
50°-60°	413.1	16.0
60°-70°	341.1	13.2
70°-80°	232.5	9.0
80°-90°	79.3	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	660.8	25.5
0°-40°	1081.4	41.8
0°-60°	1936.1	74.8
0°-90°	2589.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2589.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	854	854	854	854	854	
5°	852	851	847	852	852	81
15°	814	815	816	825	826	230
25°	743	746	755	770	774	342
35°	646	653	670	692	699	404
45°	532	543	570	601	612	410
55°	408	424	462	500	514	364
65°	276	299	347	391	406	274
75°	143	175	228	271	287	152
85°	29	58	81	91	94	37
90°	0	0	0	0	0	



TEST NUMBER: P310509

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-CP125-W2A-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	853.8	853.8	853.8	853.8	853.8
2.5°	854.7	853.8	849.5	853.8	853.0
5°	852.1	851.3	847.0	852.1	852.1
7.5°	846.1	846.1	841.8	847.8	848.7
10°	837.5	837.5	834.9	841.8	841.8
12.5°	827.2	827.2	827.2	834.1	834.9
15°	814.3	815.2	816.0	824.6	826.3
17.5°	798.9	800.6	803.1	813.5	815.2
20°	782.5	784.3	788.5	800.6	803.1
22.5°	761.9	766.2	772.2	786.0	788.5
25°	743.0	746.5	755.0	769.6	773.9
27.5°	719.8	725.0	736.1	751.6	757.6
30°	696.6	701.8	715.5	733.6	738.7
32.5°	671.7	679.5	694.1	713.0	719.0
35°	646.0	652.8	670.0	692.3	699.2
37.5°	617.6	627.1	646.0	670.0	678.6
40°	590.1	600.4	621.9	647.7	658.0
42.5°	562.6	572.9	597.0	626.2	636.5
45°	531.7	542.9	570.4	601.3	612.5
47.5°	500.8	514.5	544.6	577.2	589.3
50°	469.0	484.5	517.1	551.5	565.2
52.5°	440.7	455.3	489.6	526.6	539.4
55°	408.0	424.3	462.1	499.9	514.5
57.5°	374.5	392.6	432.9	474.2	488.8
60°	341.9	361.6	406.3	447.5	463.9
62.5°	310.1	329.8	376.2	419.2	435.5
65°	275.7	298.9	347.0	390.8	406.3
67.5°	243.1	268.0	318.7	361.6	377.1
70°	211.3	235.4	289.5	331.6	347.0
72.5°	177.0	204.4	258.6	302.4	318.7
75°	142.6	175.2	228.5	271.4	286.9
77.5°	110.8	144.3	197.6	232.8	240.5
80°	81.6	116.0	162.3	187.3	196.7
82.5°	52.4	86.8	123.7	141.7	149.5
85°	29.2	57.6	80.7	91.1	94.5
87.5°	12.0	24.9	32.6	36.9	36.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)