

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310587

Luminaire Tested: **24FCZ2-35HE-UNV-L82765-CA08-W2A-U-5700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35HE-UNV-L82765-CA08-W2A-U-5700K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.08" ACRYLIC SHEET
Light Source: (336) 5700K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3354.0 lumens
Efficiency: N/A
Efficacy: 125.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 26.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310587

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-CA08-W2A-U-5700K

Luminous Intensity Polar Plot





TEST NUMBER: P310587

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-CA08-W2A-U-5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	100	96	92	96	92	89		92	89	87		82
2	98	89	81	75	95	87	80	74	83	78	73		80	75	71		67
3	89	77	69	62	86	76	68	61	73	66	60		70	64	59		56
4	81	68	59	52	79	67	58	52	64	57	51		62	56	50		47
5	74	61	52	45	72	60	51	44	58	50	44		56	49	43		41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		36
7	64	50	41	34	62	49	40	34	47	39	34		46	39	34		31
8	59	45	37	31	57	45	36	30	43	36	30		42	35	30		28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	25		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1488	1488	1488
5°	1491	1482	1491
10°	1482	1478	1490
15°	1469	1473	1491
20°	1452	1463	1490
25°	1429	1452	1488
30°	1402	1440	1487
35°	1374	1426	1488
40°	1343	1415	1497
45°	1311	1406	1510
50°	1272	1402	1533
55°	1240	1404	1564
60°	1192	1417	1617
65°	1137	1431	1676
70°	1077	1475	1769
75°	960	1539	1932
80°	819	1629	1974
85°	584	1615	1890



TEST NUMBER: P310587

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-CA08-W2A-U-5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.7	3.1
10°-20°	299.3	8.9
20°-30°	452.1	13.5
30°-40°	544.9	16.2
40°-50°	572.0	17.1
50°-60°	535.2	16.0
60°-70°	442.0	13.2
70°-80°	301.1	9.0
80°-90°	102.7	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	856.1	25.5
0°-40°	1401.0	41.8
0°-60°	2508.2	74.8
0°-90°	3354.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3354.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1106	1106	1106	1106	1106	
5°	1104	1103	1097	1104	1104	105
15°	1055	1056	1057	1068	1070	297
25°	963	967	978	997	1003	443
35°	837	846	868	897	906	523
45°	689	703	739	779	793	531
55°	529	550	599	648	667	472
65°	357	387	450	506	526	354
75°	185	227	296	352	372	197
85°	38	75	105	118	122	47
90°	0	0	0	0	0	



TEST NUMBER: P310587

CATALOG NUMBER: 24FCZ2-35HE-UNV-L82765-CA08-W2A-U-5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1106.1	1106.1	1106.1	1106.1	1106.1
2.5°	1107.2	1106.1	1100.6	1106.1	1105.0
5°	1103.9	1102.8	1097.2	1103.9	1103.9
7.5°	1096.1	1096.1	1090.5	1098.3	1099.4
10°	1085.0	1085.0	1081.6	1090.5	1090.5
12.5°	1071.6	1071.6	1071.6	1080.5	1081.6
15°	1054.9	1056.0	1057.2	1068.3	1070.5
17.5°	1034.9	1037.1	1040.5	1053.8	1056.0
20°	1013.8	1016.0	1021.5	1037.1	1040.5
22.5°	987.1	992.6	1000.4	1018.2	1021.5
25°	962.6	967.0	978.1	997.1	1002.6
27.5°	932.5	939.2	953.7	973.7	981.5
30°	902.5	909.2	927.0	950.3	957.0
32.5°	870.2	880.2	899.1	923.6	931.4
35°	836.8	845.7	868.0	896.9	905.8
37.5°	800.1	812.3	836.8	868.0	879.1
40°	764.5	777.8	805.7	839.0	852.4
42.5°	728.9	742.2	773.4	811.2	824.6
45°	688.8	703.3	738.9	779.0	793.4
47.5°	648.8	666.6	705.5	747.8	763.4
50°	607.6	627.6	669.9	714.4	732.2
52.5°	570.9	589.8	634.3	682.1	698.8
55°	528.6	549.7	598.7	647.6	666.6
57.5°	485.2	508.5	560.8	614.3	633.2
60°	442.9	468.5	526.4	579.8	600.9
62.5°	401.7	427.3	487.4	543.0	564.2
65°	357.2	387.3	449.6	506.3	526.4
67.5°	314.9	347.2	412.8	468.5	488.5
70°	273.7	304.9	375.0	429.5	449.6
72.5°	229.2	264.8	335.0	391.7	412.8
75°	184.7	227.0	296.0	351.6	371.7
77.5°	143.6	186.9	255.9	301.6	311.6
80°	105.7	150.2	210.3	242.6	254.8
82.5°	67.9	112.4	160.2	183.6	193.6
85°	37.8	74.6	104.6	118.0	122.4
87.5°	15.6	32.3	42.3	47.9	47.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)