

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P309963

Luminaire Tested: **24FCZ2-35-UNV-L82765-RDP-CA125-W2A-U-4500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P309963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-35-UNV-L82765-RDP-CA125-W2A-U-4500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" ACRYLIC SHEET
Light Source: (168) 4500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2214.0 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 28.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P309963

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-RDP-CA125-W2A-U-4500K

Luminous Intensity Polar Plot





TEST NUMBER: P309963

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-RDP-CA125-W2A-U-4500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	100	96	92	96	93	89		92	89	87		82
2	97	89	81	75	95	87	80	74	83	77	72		80	75	71		67
3	88	77	68	62	86	76	67	61	72	66	60		70	64	59		56
4	81	68	59	52	78	67	58	51	64	57	51		62	55	50		47
5	74	60	51	44	72	59	51	44	57	49	43		55	48	43		40
6	68	54	45	38	66	53	45	38	51	44	38		50	43	37		35
7	63	49	40	34	61	48	40	34	47	39	33		45	38	33		31
8	59	45	36	30	57	44	36	30	43	35	30		41	34	29		27
9	55	41	33	27	53	40	32	27	39	32	27		38	31	26		24
10	51	38	30	24	50	37	29	24	36	29	24		35	29	24		22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	937	937	937
5°	940	934	939
10°	938	935	939
15°	936	935	941
20°	929	934	943
25°	926	936	946
30°	918	933	949
35°	909	931	952
40°	899	930	964
45°	884	930	986
50°	864	936	1016
55°	842	951	1061
60°	807	969	1120
65°	755	1004	1189
70°	687	1050	1279
75°	582	1107	1336
80°	459	1115	1081
85°	340	848	949



TEST NUMBER: P309963

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-RDP-CA125-W2A-U-4500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.0	3.0
10°-20°	190.1	8.6
20°-30°	290.7	13.1
30°-40°	355.3	16.0
40°-50°	378.7	17.1
50°-60°	362.1	16.4
60°-70°	306.7	13.9
70°-80°	206.2	9.3
80°-90°	58.2	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	546.8	24.7
0°-40°	902.1	40.7
0°-60°	1643.0	74.2
0°-90°	2214.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2214.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	696	696	696	696	696	
5°	696	695	692	695	695	66
15°	672	672	671	676	675	189
25°	624	626	630	636	637	287
35°	554	558	567	578	580	347
45°	464	472	489	510	518	358
55°	359	372	405	437	452	320
65°	237	261	315	357	373	236
75°	112	153	213	249	257	120
85°	22	45	55	59	62	27
90°	0	0	0	0	0	



TEST NUMBER: P309963

CATALOG NUMBER: 24FCZ2-35-UNV-L82765-RDP-CA125-W2A-U-4500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	696.2	696.2	696.2	696.2	696.2
2.5°	697.3	697.3	694.0	696.2	696.2
5°	696.2	695.1	691.8	695.1	695.1
7.5°	692.9	691.8	689.7	692.9	691.8
10°	686.4	686.4	684.2	687.5	687.5
12.5°	680.9	679.8	678.7	683.1	682.0
15°	672.1	672.1	671.0	676.5	675.4
17.5°	661.1	662.2	663.3	667.7	668.8
20°	649.0	651.2	652.3	658.9	658.9
22.5°	638.0	639.1	641.3	647.9	647.9
25°	623.8	626.0	630.3	635.8	636.9
27.5°	609.5	610.6	616.1	623.8	624.9
30°	590.8	594.1	600.7	609.5	610.6
32.5°	574.3	577.6	585.3	594.1	596.3
35°	553.5	557.9	566.7	577.6	579.8
37.5°	534.8	538.1	549.1	561.2	564.5
40°	511.7	518.3	529.3	543.6	549.1
42.5°	488.7	495.3	508.5	527.1	533.7
45°	464.5	472.2	488.7	509.6	518.3
47.5°	440.4	449.2	467.8	492.0	501.9
50°	412.9	423.9	447.0	474.4	485.4
52.5°	386.6	399.7	425.0	455.7	470.0
55°	359.1	372.3	405.2	437.1	452.4
57.5°	328.4	345.9	382.2	418.4	434.9
60°	299.8	316.3	360.2	399.7	416.2
62.5°	269.1	291.0	338.2	380.0	396.4
65°	237.2	261.4	315.2	356.9	373.4
67.5°	208.7	235.0	292.1	333.8	350.3
70°	174.6	207.6	266.9	308.6	325.1
72.5°	142.8	179.0	240.5	281.1	296.5
75°	112.0	152.6	213.0	249.3	257.0
77.5°	83.5	126.3	184.5	199.9	194.4
80°	59.3	101.0	143.9	136.2	139.5
82.5°	38.4	76.9	89.0	101.0	104.3
85°	22.0	45.0	54.9	59.3	61.5
87.5°	9.9	16.5	22.0	22.0	20.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)