

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310148

Luminaire Tested: **24FCZ2-45-UNV-L82765-RDP-CP125-W2A-U-2700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1808-918-19)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-45-UNV-L82765-RDP-CP125-W2A-U-2700K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS WITH INSERT, 0.125" POLYCARB SHEET
Light Source: (168) 2700K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2499.0 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.3 / 1.41
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 37.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310148

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-RDP-CP125-W2A-U-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P310148

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-RDP-CP125-W2A-U-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	100	96	92	96	93	89		92	89	87		82
2	97	89	81	75	95	87	80	74	83	77	72		80	75	71		67
3	88	77	68	62	86	76	67	61	72	66	60		70	64	59		56
4	81	68	59	52	78	67	58	51	64	57	51		62	55	50		47
5	74	60	51	44	72	59	51	44	57	49	43		55	48	43		40
6	68	54	45	38	66	53	45	38	51	44	38		50	43	37		35
7	63	49	40	34	61	48	40	34	47	39	33		45	38	33		31
8	59	45	36	30	57	44	36	30	43	35	30		41	34	29		27
9	55	41	33	27	53	40	32	27	39	32	27		38	31	26		24
10	51	38	30	24	50	37	29	24	36	29	24		35	29	24		22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1057	1057	1057
5°	1061	1055	1060
10°	1058	1055	1060
15°	1057	1055	1062
20°	1049	1054	1065
25°	1045	1056	1067
30°	1036	1053	1071
35°	1026	1051	1075
40°	1015	1049	1089
45°	998	1050	1113
50°	976	1056	1147
55°	951	1073	1198
60°	911	1094	1264
65°	852	1132	1342
70°	775	1185	1443
75°	657	1250	1508
80°	518	1258	1220
85°	383	957	1071



TEST NUMBER: P310148

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-RDP-CP125-W2A-U-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.5	3.0
10°-20°	214.5	8.6
20°-30°	328.1	13.1
30°-40°	401.1	16.0
40°-50°	427.5	17.1
50°-60°	408.7	16.4
60°-70°	346.2	13.9
70°-80°	232.7	9.3
80°-90°	65.6	2.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	617.2	24.7
0°-40°	1018.3	40.7
0°-60°	1854.5	74.2
0°-90°	2499.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2499.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	786	786	786	786	786	
5°	786	785	781	785	785	75
15°	759	759	757	764	762	214
25°	704	706	712	718	719	325
35°	625	630	640	652	654	391
45°	524	533	552	575	585	404
55°	405	420	457	493	511	361
65°	268	295	356	403	421	266
75°	126	172	240	281	290	135
85°	25	51	62	67	69	31
90°	0	0	0	0	0	



TEST NUMBER: P310148

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-RDP-CP125-W2A-U-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	785.9	785.9	785.9	785.9	785.9
2.5°	787.1	787.1	783.4	785.9	785.9
5°	785.9	784.6	780.9	784.6	784.6
7.5°	782.1	780.9	778.4	782.1	780.9
10°	774.7	774.7	772.2	775.9	775.9
12.5°	768.5	767.3	766.0	771.0	769.8
15°	758.6	758.6	757.4	763.6	762.3
17.5°	746.2	747.4	748.7	753.6	754.9
20°	732.6	735.0	736.3	743.7	743.7
22.5°	720.2	721.4	723.9	731.3	731.3
25°	704.1	706.5	711.5	717.7	718.9
27.5°	687.9	689.2	695.4	704.1	705.3
30°	666.9	670.6	678.0	687.9	689.2
32.5°	648.3	652.0	660.7	670.6	673.1
35°	624.7	629.7	639.6	652.0	654.5
37.5°	603.7	607.4	619.8	633.4	637.1
40°	577.6	585.1	597.5	613.6	619.8
42.5°	551.6	559.0	573.9	595.0	602.4
45°	524.3	533.0	551.6	575.1	585.1
47.5°	497.1	507.0	528.0	555.3	566.5
50°	466.1	478.5	504.5	535.5	547.9
52.5°	436.3	451.2	479.7	514.4	530.5
55°	405.3	420.2	457.4	493.3	510.7
57.5°	370.6	390.5	431.4	472.3	490.9
60°	338.4	357.0	406.6	451.2	469.8
62.5°	303.7	328.5	381.8	428.9	447.5
65°	267.7	295.0	355.7	402.8	421.4
67.5°	235.5	265.3	329.7	376.8	395.4
70°	197.1	234.3	301.2	348.3	366.9
72.5°	161.1	202.0	271.5	317.3	334.7
75°	126.4	172.3	240.5	281.4	290.1
77.5°	94.2	142.5	208.2	225.6	219.4
80°	66.9	114.0	162.4	153.7	157.4
82.5°	43.4	86.8	100.4	114.0	117.8
85°	24.8	50.8	62.0	66.9	69.4
87.5°	11.2	18.6	24.8	24.8	23.6
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)