

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310777

Luminaire Tested: **24FCZ2-45HE-UNV-L82765-CA125-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-45HE-UNV-L82765-CA125-W2A-U-6500K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 6500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4271.0 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 35.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310777

CATALOG NUMBER: 24FCZ2-45HE-UNV-L82765-CA125-W2A-U-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P310777

CATALOG NUMBER: 24FCZ2-45HE-UNV-L82765-CA125-W2A-U-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	100	96	92	96	92	89		92	89	87		82
2	98	89	81	75	95	87	80	74	83	78	73		80	75	71		67
3	89	77	69	62	86	76	68	61	73	66	60		70	64	59		56
4	81	68	59	52	79	67	58	52	64	57	51		62	56	50		47
5	74	61	52	45	72	60	51	44	58	50	44		56	49	43		41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		36
7	64	50	41	34	62	49	40	34	47	39	34		46	39	34		31
8	59	45	37	31	57	45	36	30	43	36	30		42	35	30		28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	25		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1895	1895	1895
5°	1899	1887	1899
10°	1888	1882	1897
15°	1871	1875	1899
20°	1848	1863	1897
25°	1820	1849	1896
30°	1785	1834	1893
35°	1750	1815	1895
40°	1710	1802	1907
45°	1669	1790	1923
50°	1620	1786	1952
55°	1579	1788	1991
60°	1518	1804	2059
65°	1448	1823	2134
70°	1371	1878	2252
75°	1223	1959	2460
80°	1043	2075	2514
85°	744	2056	2407



TEST NUMBER: P310777

CATALOG NUMBER: 24FCZ2-45HE-UNV-L82765-CA125-W2A-U-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.3	3.1
10°-20°	381.2	8.9
20°-30°	575.7	13.5
30°-40°	693.9	16.2
40°-50°	728.4	17.1
50°-60°	681.5	16.0
60°-70°	562.8	13.2
70°-80°	383.5	9.0
80°-90°	130.8	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1090.2	25.5
0°-40°	1784.0	41.8
0°-60°	3193.9	74.8
0°-90°	4271.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4271.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1408	1408	1408	1408	1408	
5°	1406	1404	1397	1406	1406	133
15°	1343	1345	1346	1360	1363	379
25°	1226	1231	1246	1270	1277	564
35°	1066	1077	1105	1142	1154	666
45°	877	896	941	992	1010	676
55°	673	700	762	825	849	601
65°	455	493	572	645	670	451
75°	235	289	377	448	473	251
85°	48	95	133	150	156	60
90°	0	0	0	0	0	



TEST NUMBER: P310777

CATALOG NUMBER: 24FCZ2-45HE-UNV-L82765-CA125-W2A-U-6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1408.5	1408.5	1408.5	1408.5	1408.5
2.5°	1410.0	1408.5	1401.5	1408.5	1407.1
5°	1405.7	1404.3	1397.2	1405.7	1405.7
7.5°	1395.8	1395.8	1388.7	1398.6	1400.0
10°	1381.6	1381.6	1377.4	1388.7	1388.7
12.5°	1364.6	1364.6	1364.6	1375.9	1377.4
15°	1343.4	1344.8	1346.2	1360.4	1363.2
17.5°	1317.8	1320.7	1324.9	1341.9	1344.8
20°	1290.9	1293.8	1300.8	1320.7	1324.9
22.5°	1256.9	1264.0	1273.9	1296.6	1300.8
25°	1225.7	1231.4	1245.6	1269.7	1276.8
27.5°	1187.5	1196.0	1214.4	1239.9	1249.8
30°	1149.2	1157.7	1180.4	1210.2	1218.7
32.5°	1108.1	1120.9	1145.0	1176.1	1186.1
35°	1065.6	1077.0	1105.3	1142.1	1153.5
37.5°	1018.9	1034.4	1065.6	1105.3	1119.5
40°	973.5	990.5	1025.9	1068.4	1085.5
42.5°	928.2	945.2	984.8	1033.0	1050.0
45°	877.1	895.6	940.9	991.9	1010.4
47.5°	826.1	848.8	898.4	952.3	972.1
50°	773.7	799.2	853.1	909.7	932.4
52.5°	726.9	751.0	807.7	868.6	889.9
55°	673.1	700.0	762.4	824.7	848.8
57.5°	617.8	647.6	714.2	782.2	806.3
60°	564.0	596.6	670.3	738.3	765.2
62.5°	511.6	544.1	620.7	691.5	718.4
65°	454.9	493.1	572.5	644.8	670.3
67.5°	401.0	442.1	525.7	596.6	622.1
70°	348.6	388.3	477.5	547.0	572.5
72.5°	291.9	337.3	426.5	498.8	525.7
75°	235.2	289.1	376.9	447.8	473.3
77.5°	182.8	238.1	325.9	384.0	396.8
80°	134.6	191.3	267.8	308.9	324.5
82.5°	86.4	143.1	204.1	233.8	246.6
85°	48.2	94.9	133.2	150.2	155.9
87.5°	19.8	41.1	53.8	60.9	60.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)