

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310861

Luminaire Tested: **24FCZ2-50HE-UNV-L82765-CA125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310861
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-50HE-UNV-L82765-CA125-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4472.0 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 38.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310861

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-CA125-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P310861

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-CA125-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	108	103	98	94	105	100	96	92	96	92	89	92	89	87	88	86	84	82		
2	98	89	81	75	95	87	80	74	83	78	73	80	75	71	77	73	69	67		
3	89	77	69	62	86	76	68	61	73	66	60	70	64	59	67	62	58	56		
4	81	68	59	52	79	67	58	52	64	57	51	62	56	50	60	54	50	47		
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41		
6	69	55	46	39	67	54	45	39	52	44	38	50	43	38	49	42	38	36		
7	64	50	41	34	62	49	40	34	47	39	34	46	39	34	44	38	33	31		
8	59	45	37	31	57	45	36	30	43	36	30	42	35	30	41	34	30	28		
9	55	41	33	27	54	41	33	27	40	32	27	39	32	27	38	31	27	25		
10	52	38	30	25	50	38	30	25	37	30	25	36	29	25	35	29	24	23		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1984	1984	1984
5°	1988	1976	1988
10°	1976	1970	1987
15°	1959	1963	1988
20°	1935	1950	1986
25°	1905	1936	1985
30°	1869	1920	1982
35°	1833	1901	1984
40°	1790	1887	1996
45°	1748	1875	2013
50°	1696	1870	2044
55°	1653	1872	2085
60°	1589	1889	2156
65°	1516	1908	2234
70°	1436	1967	2358
75°	1280	2052	2576
80°	1093	2173	2633
85°	778	2154	2519



TEST NUMBER: P310861

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-CA125-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.6	3.1
10°-20°	399.1	8.9
20°-30°	602.8	13.5
30°-40°	726.5	16.2
40°-50°	762.7	17.1
50°-60°	713.6	16.0
60°-70°	589.3	13.2
70°-80°	401.5	9.0
80°-90°	137.0	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1141.5	25.5
0°-40°	1868.0	41.8
0°-60°	3344.2	74.8
0°-90°	4472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4472.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1475	1475	1475	1475	1475	
5°	1472	1470	1463	1472	1472	140
15°	1407	1408	1410	1424	1427	396
25°	1283	1289	1304	1329	1337	591
35°	1116	1128	1157	1196	1208	697
45°	918	938	985	1039	1058	708
55°	705	733	798	864	889	629
65°	476	516	599	675	702	472
75°	246	303	395	469	496	263
85°	50	99	140	157	163	63
90°	0	0	0	0	0	



TEST NUMBER: P310861

CATALOG NUMBER: 24FCZ2-50HE-UNV-L82765-CA125-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.8	1474.8	1474.8	1474.8	1474.8
2.5°	1476.3	1474.8	1467.4	1474.8	1473.3
5°	1471.9	1470.4	1463.0	1471.9	1471.9
7.5°	1461.5	1461.5	1454.1	1464.4	1465.9
10°	1446.6	1446.6	1442.2	1454.1	1454.1
12.5°	1428.8	1428.8	1428.8	1440.7	1442.2
15°	1406.6	1408.1	1409.5	1424.4	1427.3
17.5°	1379.9	1382.8	1387.3	1405.1	1408.1
20°	1351.7	1354.6	1362.1	1382.8	1387.3
22.5°	1316.1	1323.5	1333.9	1357.6	1362.1
25°	1283.4	1289.4	1304.2	1329.4	1336.8
27.5°	1243.4	1252.3	1271.6	1298.3	1308.6
30°	1203.3	1212.2	1235.9	1267.1	1276.0
32.5°	1160.3	1173.6	1198.9	1231.5	1241.9
35°	1115.8	1127.6	1157.3	1195.9	1207.8
37.5°	1066.8	1083.1	1115.8	1157.3	1172.1
40°	1019.3	1037.1	1074.2	1118.7	1136.5
42.5°	971.8	989.6	1031.2	1081.6	1099.4
45°	918.4	937.7	985.2	1038.6	1057.9
47.5°	865.0	888.8	940.7	997.1	1017.8
50°	810.1	836.8	893.2	952.6	976.3
52.5°	761.2	786.4	845.7	909.5	931.8
55°	704.8	733.0	798.2	863.5	888.8
57.5°	646.9	678.1	747.8	819.0	844.2
60°	590.5	624.6	701.8	773.0	801.2
62.5°	535.6	569.8	649.9	724.1	752.3
65°	476.3	516.3	599.4	675.1	701.8
67.5°	419.9	462.9	550.5	624.6	651.4
70°	365.0	406.5	500.0	572.7	599.4
72.5°	305.6	353.1	446.6	522.3	550.5
75°	246.3	302.7	394.7	468.9	495.6
77.5°	191.4	249.3	341.3	402.1	415.4
80°	141.0	200.3	280.4	323.5	339.8
82.5°	90.5	149.9	213.7	244.8	258.2
85°	50.4	99.4	139.5	157.3	163.2
87.5°	20.8	43.0	56.4	63.8	63.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)