

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310534

Luminaire Tested: **24FCZ2-30HE-UNV-L82765-CP250-W2A-U-6500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-30HE-UNV-L82765-CP250-W2A-U-6500K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.250" POLYCARB SHEET
Light Source: (336) 6500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2723.0 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310534

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-CP250-W2A-U-6500K

Luminous Intensity Polar Plot





TEST NUMBER: P310534

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-CP250-W2A-U-6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	100	96	92	96	92	89		92	89	87		82
2	98	89	81	75	95	87	80	74	83	78	73		80	75	71		67
3	89	77	69	62	86	76	68	61	73	66	60		70	64	59		56
4	81	68	59	52	79	67	58	52	64	57	51		62	56	50		47
5	74	61	52	45	72	60	51	44	58	50	44		56	49	43		41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		36
7	64	50	41	34	62	49	40	34	47	39	34		46	39	34		31
8	59	45	37	31	57	45	36	30	43	36	30		42	35	30		28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	25		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1208	1208	1208
5°	1210	1203	1210
10°	1204	1200	1210
15°	1193	1196	1211
20°	1178	1188	1209
25°	1160	1179	1208
30°	1138	1169	1207
35°	1116	1157	1208
40°	1090	1149	1215
45°	1064	1141	1226
50°	1033	1138	1244
55°	1007	1140	1270
60°	968	1150	1313
65°	923	1162	1360
70°	874	1198	1436
75°	780	1249	1568
80°	665	1323	1603
85°	474	1311	1535



TEST NUMBER: P310534

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-CP250-W2A-U-6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	3.1
10°-20°	243.0	8.9
20°-30°	367.0	13.5
30°-40°	442.4	16.2
40°-50°	464.4	17.1
50°-60°	434.5	16.0
60°-70°	358.8	13.2
70°-80°	244.5	9.0
80°-90°	83.4	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	695.0	25.5
0°-40°	1137.4	41.8
0°-60°	2036.3	74.8
0°-90°	2723.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2723.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	898	898	898	898	898	
5°	896	895	891	896	896	85
15°	856	857	858	867	869	241
25°	782	785	794	810	814	360
35°	679	687	705	728	735	425
45°	559	571	600	632	644	431
55°	429	446	486	526	541	383
65°	290	314	365	411	427	288
75°	150	184	240	286	302	160
85°	31	60	85	96	99	38
90°	0	0	0	0	0	



TEST NUMBER: P310534

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-CP250-W2A-U-6500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	898.0	898.0	898.0	898.0	898.0
2.5°	898.9	898.0	893.5	898.0	897.1
5°	896.2	895.3	890.8	896.2	896.2
7.5°	889.9	889.9	885.4	891.7	892.6
10°	880.9	880.9	878.1	885.4	885.4
12.5°	870.0	870.0	870.0	877.2	878.1
15°	856.5	857.4	858.3	867.3	869.1
17.5°	840.2	842.0	844.7	855.6	857.4
20°	823.0	824.8	829.4	842.0	844.7
22.5°	801.4	805.9	812.2	826.6	829.4
25°	781.5	785.1	794.1	809.5	814.0
27.5°	757.1	762.5	774.3	790.5	796.8
30°	732.7	738.1	752.6	771.5	777.0
32.5°	706.5	714.6	730.0	749.9	756.2
35°	679.4	686.6	704.7	728.2	735.4
37.5°	649.6	659.5	679.4	704.7	713.7
40°	620.7	631.5	654.1	681.2	692.0
42.5°	591.8	602.6	627.9	658.6	669.5
45°	559.2	571.0	599.9	632.4	644.2
47.5°	526.7	541.2	572.8	607.1	619.8
50°	493.3	509.5	543.9	580.0	594.5
52.5°	463.5	478.8	515.0	553.8	567.4
55°	429.1	446.3	486.1	525.8	541.2
57.5°	393.9	412.9	455.3	498.7	514.1
60°	359.6	380.3	427.3	470.7	487.9
62.5°	326.1	346.9	395.7	440.9	458.0
65°	290.0	314.4	365.0	411.1	427.3
67.5°	255.7	281.9	335.2	380.3	396.6
70°	222.2	247.5	304.5	348.7	365.0
72.5°	186.1	215.0	271.9	318.0	335.2
75°	150.0	184.3	240.3	285.5	301.7
77.5°	116.5	151.8	207.8	244.8	253.0
80°	85.8	122.0	170.8	197.0	206.9
82.5°	55.1	91.2	130.1	149.1	157.2
85°	30.7	60.5	84.9	95.8	99.4
87.5°	12.6	26.2	34.3	38.8	38.8
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)