

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311226

Luminaire Tested: **24FCZ2-30-UNV-L82765-S-CA125-W2A-U-5700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P311226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-30-UNV-L82765-S-CA125-W2A-U-5700K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" ACRYLIC SHEET
Light Source: (168) 5700K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3027.0 lumens
Efficiency: N/A
Efficacy: 125.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 24.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P311226

CATALOG NUMBER: 24FCZ2-30-UNV-L82765-S-CA125-W2A-U-5700K

Luminous Intensity Polar Plot





TEST NUMBER: P311226

CATALOG NUMBER: 24FCZ2-30-UNV-L82765-S-CA125-W2A-U-5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		69
3	89	79	70	64	87	77	69	63	74	67	62		71	66	61		58
4	82	70	61	54	80	68	60	54	66	59	53		63	57	52		49
5	75	62	53	46	73	61	53	46	59	51	46		57	50	45		42
6	70	56	47	40	68	55	47	40	53	46	40		52	45	40		37
7	64	51	42	36	63	50	42	36	48	41	35		47	40	35		33
8	60	46	38	32	58	46	37	32	44	37	32		43	36	31		29
9	56	43	34	29	55	42	34	29	41	34	28		40	33	28		26
10	53	39	31	26	51	39	31	26	38	31	26		37	30	26		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1431	1431	1431
5°	1430	1426	1435
10°	1424	1424	1434
15°	1410	1417	1432
20°	1392	1406	1428
25°	1366	1392	1419
30°	1336	1376	1407
35°	1306	1353	1396
40°	1261	1331	1380
45°	1220	1304	1365
50°	1173	1280	1348
55°	1121	1256	1335
60°	1069	1237	1333
65°	1001	1215	1341
70°	927	1222	1377
75°	830	1245	1455
80°	670	1319	1423
85°	505	1158	1129



TEST NUMBER: P311226

CATALOG NUMBER: 24FCZ2-30-UNV-L82765-S-CA125-W2A-U-5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.7	3.3
10°-20°	287.7	9.5
20°-30°	432.4	14.3
30°-40°	515.1	17.0
40°-50°	527.2	17.4
50°-60°	474.6	15.7
60°-70°	372.7	12.3
70°-80°	241.9	8.0
80°-90°	74.8	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	820.8	27.1
0°-40°	1335.8	44.1
0°-60°	2337.6	77.2
0°-90°	3027.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3027.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1059	1060	1056	1062	1062	101
15°	1012	1015	1017	1026	1028	285
25°	920	928	938	953	956	424
35°	795	805	824	844	850	496
45°	641	657	686	712	717	494
55°	478	499	536	563	569	428
65°	314	338	382	413	421	313
75°	160	190	239	272	280	169
85°	33	61	75	73	73	39
90°	0	0	0	0	0	



TEST NUMBER: P311226

CATALOG NUMBER: 24FCZ2-30-UNV-L82765-S-CA125-W2A-U-5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1063.4	1063.4	1063.4	1063.4	1063.4
2.5°	1064.4	1064.4	1059.6	1064.4	1065.3
5°	1058.6	1060.5	1055.7	1061.5	1062.4
7.5°	1052.8	1052.8	1049.9	1055.7	1056.7
10°	1042.3	1043.2	1042.3	1049.0	1049.9
12.5°	1028.8	1030.7	1031.7	1038.4	1039.4
15°	1012.4	1015.3	1017.3	1025.9	1027.8
17.5°	994.2	997.1	1001.9	1011.5	1013.4
20°	972.1	975.9	981.7	994.2	997.1
22.5°	948.0	951.9	961.5	973.0	977.8
25°	920.1	927.8	937.5	952.8	955.7
27.5°	892.3	899.0	911.5	927.8	931.7
30°	859.6	870.1	885.5	901.9	905.7
32.5°	827.8	838.4	856.7	874.0	878.8
35°	795.1	804.8	824.0	844.2	850.0
37.5°	757.7	770.2	791.3	811.5	817.3
40°	718.2	733.6	757.7	778.8	785.5
42.5°	680.7	697.1	721.1	744.2	751.9
45°	641.3	656.7	685.5	711.5	717.3
47.5°	600.9	618.2	649.0	675.0	684.6
50°	560.5	578.8	611.5	638.4	644.2
52.5°	520.2	539.4	574.0	602.9	605.7
55°	477.9	499.0	535.5	563.4	569.2
57.5°	439.4	457.7	497.1	525.9	532.7
60°	397.1	417.3	459.6	486.5	495.2
62.5°	356.7	377.9	422.1	449.0	456.7
65°	314.4	338.4	381.7	413.4	421.1
67.5°	277.9	300.9	347.1	377.9	385.6
70°	235.6	261.5	310.6	342.3	350.0
72.5°	199.0	225.9	275.0	305.8	317.3
75°	159.6	190.4	239.4	272.1	279.8
77.5°	121.1	156.7	206.7	231.7	231.7
80°	86.5	124.0	170.2	181.7	183.6
82.5°	56.7	93.3	126.0	125.0	125.0
85°	32.7	60.6	75.0	73.1	73.1
87.5°	12.5	25.0	26.9	26.9	26.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)