

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310681

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-CA125-W2A-U-3500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310681
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L82765-CA125-W2A-U-3500K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 3500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3624.0 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 30.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310681

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA125-W2A-U-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P310681

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA125-W2A-U-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	108	103	98	94	105	100	96	92		96	92	89		92	89	87		88	86	84
2	98	89	81	75	95	87	80	74		83	78	73		80	75	71		77	73	69
3	89	77	69	62	86	76	68	61		73	66	60		70	64	59		67	62	58
4	81	68	59	52	79	67	58	52		64	57	51		62	56	50		60	54	50
5	74	61	52	45	72	60	51	44		58	50	44		56	49	43		54	48	43
6	69	55	46	39	67	54	45	39		52	44	38		50	43	38		49	42	38
7	64	50	41	34	62	49	40	34		47	39	34		46	39	34		44	38	33
8	59	45	37	31	57	45	36	30		43	36	30		42	35	30		41	34	30
9	55	41	33	27	54	41	33	27		40	32	27		39	32	27		38	31	27
10	52	38	30	25	50	38	30	25		37	30	25		36	29	25		35	29	24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1608	1608	1608
5°	1611	1601	1611
10°	1602	1597	1610
15°	1588	1591	1611
20°	1568	1580	1610
25°	1544	1569	1608
30°	1515	1556	1606
35°	1485	1541	1608
40°	1451	1529	1618
45°	1416	1519	1631
50°	1374	1515	1656
55°	1340	1517	1689
60°	1288	1530	1747
65°	1229	1547	1811
70°	1164	1594	1911
75°	1038	1663	2088
80°	885	1760	2133
85°	631	1744	2042



TEST NUMBER: P310681

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA125-W2A-U-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.1	3.1
10°-20°	323.4	8.9
20°-30°	488.5	13.5
30°-40°	588.7	16.2
40°-50°	618.1	17.1
50°-60°	578.3	16.0
60°-70°	477.5	13.2
70°-80°	325.4	9.0
80°-90°	111.0	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	925.0	25.5
0°-40°	1513.8	41.8
0°-60°	2710.1	74.8
0°-90°	3624.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3624.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1195	1195	1195	1195	1195	
5°	1193	1192	1186	1193	1193	113
15°	1140	1141	1142	1154	1157	321
25°	1040	1045	1057	1077	1083	479
35°	904	914	938	969	979	565
45°	744	760	798	842	857	574
55°	571	594	647	700	720	510
65°	386	418	486	547	569	383
75°	200	245	320	380	402	213
85°	41	81	113	128	132	51
90°	0	0	0	0	0	



TEST NUMBER: P310681

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA125-W2A-U-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1195.2	1195.2	1195.2	1195.2	1195.2
2.5°	1196.4	1195.2	1189.2	1195.2	1194.0
5°	1192.8	1191.6	1185.5	1192.8	1192.8
7.5°	1184.3	1184.3	1178.3	1186.7	1187.9
10°	1172.3	1172.3	1168.7	1178.3	1178.3
12.5°	1157.9	1157.9	1157.9	1167.5	1168.7
15°	1139.9	1141.1	1142.3	1154.3	1156.7
17.5°	1118.2	1120.6	1124.2	1138.7	1141.1
20°	1095.4	1097.8	1103.8	1120.6	1124.2
22.5°	1066.5	1072.5	1080.9	1100.2	1103.8
25°	1040.1	1044.9	1056.9	1077.3	1083.3
27.5°	1007.6	1014.8	1030.4	1052.1	1060.5
30°	975.1	982.3	1001.6	1026.8	1034.0
32.5°	940.3	951.1	971.5	998.0	1006.4
35°	904.2	913.8	937.9	969.1	978.7
37.5°	864.5	877.7	904.2	937.9	949.9
40°	826.0	840.5	870.5	906.6	921.0
42.5°	787.6	802.0	835.7	876.5	891.0
45°	744.3	759.9	798.4	841.7	857.3
47.5°	701.0	720.2	762.3	808.0	824.8
50°	656.5	678.1	723.8	771.9	791.2
52.5°	616.8	637.3	685.4	737.1	755.1
55°	571.1	594.0	646.9	699.8	720.2
57.5°	524.2	549.5	606.0	663.7	684.2
60°	478.5	506.2	568.7	626.4	649.3
62.5°	434.1	461.7	526.6	586.8	609.6
65°	386.0	418.4	485.8	547.1	568.7
67.5°	340.3	375.1	446.1	506.2	527.8
70°	295.8	329.5	405.2	464.1	485.8
72.5°	247.7	286.2	361.9	423.2	446.1
75°	199.6	245.3	319.8	380.0	401.6
77.5°	155.1	202.0	276.5	325.8	336.7
80°	114.2	162.3	227.2	262.1	275.3
82.5°	73.3	121.4	173.1	198.4	209.2
85°	40.9	80.6	113.0	127.5	132.3
87.5°	16.8	34.9	45.7	51.7	51.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)