

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311177

Luminaire Tested: **24FCZ2-30HE-UNV-L82765-S-CA125-W2A-U-4000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P311177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-30HE-UNV-L82765-S-CA125-W2A-U-4000K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 4000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2933.0 lumens
Efficiency: N/A
Efficacy: 137.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 21.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P311177

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-S-CA125-W2A-U-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P311177

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-S-CA125-W2A-U-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		69
3	89	79	70	64	87	77	69	63	74	67	62		71	66	61		58
4	82	70	61	54	80	68	60	54	66	59	53		63	57	52		49
5	75	62	53	46	73	61	53	46	59	51	46		57	50	45		42
6	70	56	47	40	68	55	47	40	53	46	40		52	45	40		37
7	64	51	42	36	63	50	42	36	48	41	35		47	40	35		33
8	60	46	38	32	58	46	37	32	44	37	32		43	36	31		29
9	56	43	34	29	55	42	34	29	41	34	28		40	33	28		26
10	53	39	31	26	51	39	31	26	38	31	26		37	30	26		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1386	1386	1386
5°	1385	1382	1390
10°	1380	1380	1390
15°	1366	1373	1387
20°	1349	1362	1383
25°	1324	1348	1375
30°	1294	1333	1363
35°	1266	1311	1353
40°	1222	1289	1337
45°	1182	1264	1322
50°	1137	1240	1307
55°	1086	1217	1294
60°	1035	1198	1291
65°	970	1178	1299
70°	898	1184	1334
75°	804	1206	1409
80°	649	1278	1378
85°	489	1122	1093



TEST NUMBER: P311177

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-S-CA125-W2A-U-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.5	3.3
10°-20°	278.7	9.5
20°-30°	419.0	14.3
30°-40°	499.1	17.0
40°-50°	510.8	17.4
50°-60°	459.9	15.7
60°-70°	361.1	12.3
70°-80°	234.4	8.0
80°-90°	72.5	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	795.3	27.1
0°-40°	1294.3	44.1
0°-60°	2265.0	77.2
0°-90°	2933.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2933.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1030	1030	1030	1030	1030	
5°	1026	1028	1023	1028	1030	97
15°	981	984	986	994	996	277
25°	892	899	908	923	926	411
35°	770	780	798	818	824	481
45°	621	636	664	689	695	479
55°	463	484	519	546	552	415
65°	305	328	370	401	408	303
75°	155	184	232	264	271	164
85°	32	59	73	71	71	38
90°	0	0	0	0	0	



TEST NUMBER: P311177

CATALOG NUMBER: 24FCZ2-30HE-UNV-L82765-S-CA125-W2A-U-4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1030.4	1030.4	1030.4	1030.4	1030.4
2.5°	1031.3	1031.3	1026.7	1031.3	1032.2
5°	1025.7	1027.6	1022.9	1028.5	1029.5
7.5°	1020.1	1020.1	1017.3	1022.9	1023.9
10°	1009.9	1010.8	1009.9	1016.4	1017.3
12.5°	996.8	998.7	999.6	1006.2	1007.1
15°	981.0	983.8	985.7	994.0	995.9
17.5°	963.3	966.1	970.8	980.1	981.9
20°	941.9	945.6	951.2	963.3	966.1
22.5°	918.6	922.3	931.6	942.8	947.5
25°	891.6	899.0	908.3	923.2	926.0
27.5°	864.6	871.1	883.2	899.0	902.7
30°	832.9	843.1	858.0	873.9	877.6
32.5°	802.1	812.4	830.1	846.9	851.5
35°	770.5	779.8	798.4	818.0	823.6
37.5°	734.1	746.2	766.7	786.3	791.9
40°	695.9	710.8	734.1	754.6	761.1
42.5°	659.6	675.4	698.7	721.1	728.5
45°	621.4	636.3	664.3	689.4	695.0
47.5°	582.3	599.0	628.8	654.0	663.3
50°	543.1	560.8	592.5	618.6	624.2
52.5°	504.0	522.6	556.2	584.1	586.9
55°	463.0	483.5	518.9	545.9	551.5
57.5°	425.8	443.5	481.7	509.6	516.1
60°	384.8	404.3	445.3	471.4	479.8
62.5°	345.6	366.1	409.0	435.1	442.5
65°	304.6	327.9	369.9	400.6	408.1
67.5°	269.2	291.6	336.3	366.1	373.6
70°	228.2	253.4	300.9	331.7	339.1
72.5°	192.8	218.9	266.4	296.3	307.4
75°	154.7	184.5	232.0	263.7	271.1
77.5°	117.4	151.9	200.3	224.5	224.5
80°	83.8	120.2	164.9	176.1	177.9
82.5°	55.0	90.4	122.0	121.1	121.1
85°	31.7	58.7	72.7	70.8	70.8
87.5°	12.1	24.2	26.1	26.1	25.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)