

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310684

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-CA125-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L82765-CA125-W2A-U-5000K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 5000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3821.0 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 31.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310684

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA125-W2A-U-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P310684

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA125-W2A-U-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	100	96	92	96	92	89		92	89	87		82
2	98	89	81	75	95	87	80	74	83	78	73		80	75	71		67
3	89	77	69	62	86	76	68	61	73	66	60		70	64	59		56
4	81	68	59	52	79	67	58	52	64	57	51		62	56	50		47
5	74	61	52	45	72	60	51	44	58	50	44		56	49	43		41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		36
7	64	50	41	34	62	49	40	34	47	39	34		46	39	34		31
8	59	45	37	31	57	45	36	30	43	36	30		42	35	30		28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	25		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1695	1695	1695
5°	1699	1688	1699
10°	1689	1683	1697
15°	1674	1678	1699
20°	1654	1666	1697
25°	1628	1654	1696
30°	1597	1641	1694
35°	1566	1624	1695
40°	1530	1612	1706
45°	1493	1602	1720
50°	1449	1598	1746
55°	1413	1600	1781
60°	1358	1614	1842
65°	1295	1631	1909
70°	1227	1681	2015
75°	1094	1753	2201
80°	933	1857	2249
85°	665	1840	2154



TEST NUMBER: P310684

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA125-W2A-U-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.3	3.1
10°-20°	341.0	8.9
20°-30°	515.0	13.5
30°-40°	620.7	16.2
40°-50°	651.7	17.1
50°-60°	609.7	16.0
60°-70°	503.5	13.2
70°-80°	343.1	9.0
80°-90°	117.0	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	975.3	25.5
0°-40°	1596.0	41.8
0°-60°	2857.4	74.8
0°-90°	3821.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3821.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1260	1260	1260	1260	1260	
5°	1258	1256	1250	1258	1258	119
15°	1202	1203	1204	1217	1220	339
25°	1097	1102	1114	1136	1142	505
35°	953	964	989	1022	1032	596
45°	785	801	842	887	904	605
55°	602	626	682	738	759	537
65°	407	441	512	577	600	404
75°	210	259	337	401	423	224
85°	43	85	119	134	140	54
90°	0	0	0	0	0	



TEST NUMBER: P310684

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-CA125-W2A-U-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1260.1	1260.1	1260.1	1260.1	1260.1
2.5°	1261.4	1260.1	1253.8	1260.1	1258.9
5°	1257.6	1256.3	1250.0	1257.6	1257.6
7.5°	1248.7	1248.7	1242.4	1251.3	1252.5
10°	1236.0	1236.0	1232.2	1242.4	1242.4
12.5°	1220.8	1220.8	1220.8	1231.0	1232.2
15°	1201.8	1203.1	1204.4	1217.0	1219.6
17.5°	1179.0	1181.5	1185.3	1200.5	1203.1
20°	1154.9	1157.4	1163.8	1181.5	1185.3
22.5°	1124.5	1130.8	1139.7	1160.0	1163.8
25°	1096.6	1101.7	1114.3	1135.9	1142.2
27.5°	1062.4	1070.0	1086.5	1109.3	1118.1
30°	1028.1	1035.7	1056.0	1082.6	1090.3
32.5°	991.4	1002.8	1024.3	1052.2	1061.1
35°	953.3	963.5	988.8	1021.8	1031.9
37.5°	911.5	925.4	953.3	988.8	1001.5
40°	870.9	886.1	917.8	955.9	971.1
42.5°	830.4	845.6	881.1	924.2	939.4
45°	784.7	801.2	841.8	887.4	903.9
47.5°	739.1	759.4	803.7	851.9	869.7
50°	692.2	715.0	763.2	813.9	834.2
52.5°	650.4	671.9	722.6	777.1	796.1
55°	602.2	626.3	682.0	737.8	759.4
57.5°	552.7	579.4	638.9	699.8	721.3
60°	504.6	533.7	599.6	660.5	684.6
62.5°	457.7	486.8	555.3	618.7	642.7
65°	406.9	441.2	512.2	576.8	599.6
67.5°	358.8	395.5	470.3	533.7	556.5
70°	311.9	347.4	427.2	489.3	512.2
72.5°	261.2	301.7	381.6	446.2	470.3
75°	210.4	258.6	337.2	400.6	423.4
77.5°	163.5	213.0	291.6	343.6	355.0
80°	120.4	171.1	239.6	276.4	290.3
82.5°	77.3	128.0	182.6	209.2	220.6
85°	43.1	84.9	119.2	134.4	139.5
87.5°	17.7	36.8	48.2	54.5	54.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)