

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311359

Luminaire Tested: **24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-5000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P311359
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-5000K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" ACRYLIC SHEET
Light Source: (336) 5000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4015.0 lumens
Efficiency: N/A
Efficacy: 129.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 31.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P311359

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P311359

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		69
3	89	79	70	64	87	77	69	63	74	67	62		71	66	61		58
4	82	70	61	54	80	68	60	54	66	59	53		63	57	52		49
5	75	62	53	46	73	61	53	46	59	51	46		57	50	45		42
6	70	56	47	40	68	55	47	40	53	46	40		52	45	40		37
7	64	51	42	36	63	50	42	36	48	41	35		47	40	35		33
8	60	46	38	32	58	46	37	32	44	37	32		43	36	31		29
9	56	43	34	29	55	42	34	29	41	34	28		40	33	28		26
10	53	39	31	26	51	39	31	26	38	31	26		37	30	26		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1898	1898	1898
5°	1896	1891	1903
10°	1889	1889	1903
15°	1871	1880	1899
20°	1846	1864	1894
25°	1812	1846	1882
30°	1771	1825	1866
35°	1732	1795	1852
40°	1673	1765	1830
45°	1619	1730	1810
50°	1556	1698	1789
55°	1487	1666	1771
60°	1417	1640	1767
65°	1328	1612	1778
70°	1229	1620	1826
75°	1101	1651	1929
80°	890	1749	1888
85°	670	1536	1496



TEST NUMBER: P311359

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.5	3.3
10°-20°	381.5	9.5
20°-30°	573.6	14.3
30°-40°	683.2	17.0
40°-50°	699.2	17.4
50°-60°	629.5	15.7
60°-70°	494.4	12.3
70°-80°	320.9	8.0
80°-90°	99.2	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1088.6	27.1
0°-40°	1771.8	44.1
0°-60°	3100.5	77.2
0°-90°	4015.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4015.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1410	1410	1410	1410	1410	
5°	1404	1407	1400	1408	1409	133
15°	1343	1347	1349	1361	1363	379
25°	1220	1231	1243	1264	1268	562
35°	1055	1067	1093	1120	1127	658
45°	851	871	909	944	951	656
55°	634	662	710	747	755	568
65°	417	449	506	548	559	415
75°	212	252	318	361	371	224
85°	43	80	100	97	97	52
90°	0	0	0	0	0	



TEST NUMBER: P311359

CATALOG NUMBER: 24FCZ2-40HE-UNV-L82765-S-CA125-W2A-U-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1410.5	1410.5	1410.5	1410.5	1410.5
2.5°	1411.8	1411.8	1405.4	1411.8	1413.0
5°	1404.1	1406.7	1400.3	1407.9	1409.2
7.5°	1396.5	1396.5	1392.6	1400.3	1401.6
10°	1382.4	1383.7	1382.4	1391.4	1392.6
12.5°	1364.6	1367.1	1368.4	1377.3	1378.6
15°	1342.9	1346.7	1349.3	1360.8	1363.3
17.5°	1318.7	1322.5	1328.9	1341.6	1344.2
20°	1289.3	1294.4	1302.1	1318.7	1322.5
22.5°	1257.5	1262.6	1275.3	1290.6	1297.0
25°	1220.5	1230.7	1243.4	1263.8	1267.7
27.5°	1183.5	1192.4	1209.0	1230.7	1235.8
30°	1140.1	1154.2	1174.6	1196.2	1201.3
32.5°	1098.0	1112.1	1136.3	1159.3	1165.6
35°	1054.7	1067.4	1092.9	1119.7	1127.4
37.5°	1004.9	1021.5	1049.6	1076.4	1084.0
40°	952.7	973.1	1004.9	1033.0	1041.9
42.5°	902.9	924.6	956.5	987.1	997.3
45°	850.6	871.0	909.3	943.7	951.4
47.5°	797.1	820.0	860.8	895.3	908.0
50°	743.5	767.7	811.1	846.8	854.5
52.5°	689.9	715.5	761.4	799.6	803.4
55°	633.8	661.9	710.3	747.3	755.0
57.5°	582.8	607.0	659.3	697.6	706.5
60°	526.7	553.5	609.6	645.3	656.8
62.5°	473.1	501.2	559.9	595.6	605.8
65°	417.0	448.9	506.3	548.4	558.6
67.5°	368.6	399.2	460.4	501.2	511.4
70°	312.5	346.9	411.9	454.0	464.2
72.5°	264.0	299.7	364.7	405.5	420.9
75°	211.7	252.5	317.6	360.9	371.1
77.5°	160.7	207.9	274.2	307.4	307.4
80°	114.8	164.5	225.7	241.0	243.6
82.5°	75.2	123.7	167.1	165.8	165.8
85°	43.4	80.3	99.5	96.9	96.9
87.5°	16.6	33.2	35.7	35.7	34.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)