

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311495

Luminaire Tested: **24FCZ2-45-UNV-L82765-S-CA125-W2A-U-5500K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P311495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-45-UNV-L82765-S-CA125-W2A-U-5500K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" ACRYLIC SHEET
Light Source: (168) 5500K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4511.0 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P311495

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-S-CA125-W2A-U-5500K

Luminous Intensity Polar Plot





TEST NUMBER: P311495

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-S-CA125-W2A-U-5500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		69
3	89	79	70	64	87	77	69	63	74	67	62		71	66	61		58
4	82	70	61	54	80	68	60	54	66	59	53		63	57	52		49
5	75	62	53	46	73	61	53	46	59	51	46		57	50	45		42
6	70	56	47	40	68	55	47	40	53	46	40		52	45	40		37
7	64	51	42	36	63	50	42	36	48	41	35		47	40	35		33
8	60	46	38	32	58	46	37	32	44	37	32		43	36	31		29
9	56	43	34	29	55	42	34	29	41	34	28		40	33	28		26
10	53	39	31	26	51	39	31	26	38	31	26		37	30	26		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2132	2132	2132
5°	2131	2125	2138
10°	2122	2122	2138
15°	2102	2112	2134
20°	2074	2095	2128
25°	2036	2074	2114
30°	1990	2050	2097
35°	1946	2017	2080
40°	1880	1983	2056
45°	1819	1944	2034
50°	1749	1908	2009
55°	1670	1872	1990
60°	1593	1843	1986
65°	1492	1811	1998
70°	1381	1821	2052
75°	1237	1855	2168
80°	1000	1965	2121
85°	752	1726	1681



TEST NUMBER: P311495

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-S-CA125-W2A-U-5500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.0	3.3
10°-20°	428.7	9.5
20°-30°	644.4	14.3
30°-40°	767.6	17.0
40°-50°	785.6	17.4
50°-60°	707.3	15.7
60°-70°	555.4	12.3
70°-80°	360.5	8.0
80°-90°	111.5	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1223.1	27.1
0°-40°	1990.7	44.1
0°-60°	3483.6	77.2
0°-90°	4511.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4511.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1585	1585	1585	1585	1585	
5°	1578	1580	1573	1582	1583	150
15°	1509	1513	1516	1529	1532	425
25°	1371	1383	1397	1420	1424	632
35°	1185	1199	1228	1258	1267	739
45°	956	979	1022	1060	1069	737
55°	712	744	798	840	848	638
65°	468	504	569	616	628	466
75°	238	284	357	406	417	252
85°	49	90	112	109	109	59
90°	0	0	0	0	0	



TEST NUMBER: P311495

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-S-CA125-W2A-U-5500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1584.7	1584.7	1584.7	1584.7	1584.7
2.5°	1586.2	1586.2	1579.0	1586.2	1587.6
5°	1577.6	1580.4	1573.3	1581.9	1583.3
7.5°	1569.0	1569.0	1564.7	1573.3	1574.7
10°	1553.2	1554.7	1553.2	1563.3	1564.7
12.5°	1533.2	1536.0	1537.5	1547.5	1548.9
15°	1508.8	1513.1	1516.0	1528.9	1531.7
17.5°	1481.6	1485.9	1493.0	1507.4	1510.2
20°	1448.6	1454.4	1463.0	1481.6	1485.9
22.5°	1412.8	1418.5	1432.9	1450.1	1457.2
25°	1371.2	1382.7	1397.0	1420.0	1424.3
27.5°	1329.7	1339.7	1358.4	1382.7	1388.4
30°	1281.0	1296.7	1319.7	1344.0	1349.8
32.5°	1233.7	1249.5	1276.7	1302.5	1309.6
35°	1185.0	1199.3	1228.0	1258.1	1266.6
37.5°	1129.1	1147.7	1179.2	1209.3	1217.9
40°	1070.3	1093.3	1129.1	1160.6	1170.6
42.5°	1014.5	1038.8	1074.6	1109.0	1120.5
45°	955.7	978.6	1021.6	1060.3	1068.9
47.5°	895.5	921.3	967.2	1005.9	1020.2
50°	835.4	862.6	911.3	951.4	960.0
52.5°	775.2	803.8	855.4	898.4	902.7
55°	712.1	743.7	798.1	839.7	848.3
57.5°	654.8	682.0	740.8	783.8	793.8
60°	591.8	621.9	684.9	725.0	737.9
62.5°	531.6	563.1	629.0	669.1	680.6
65°	468.5	504.4	568.8	616.1	627.6
67.5°	414.1	448.5	517.3	563.1	574.6
70°	351.1	389.7	462.8	510.1	521.6
72.5°	296.6	336.7	409.8	455.6	472.8
75°	237.9	283.7	356.8	405.5	417.0
77.5°	180.5	233.6	308.1	345.3	345.3
80°	129.0	184.8	253.6	270.8	273.7
82.5°	84.5	139.0	187.7	186.3	186.3
85°	48.7	90.3	111.8	108.9	108.9
87.5°	18.6	37.3	40.1	40.1	38.7
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)