

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311598

Luminaire Tested: **24FCZ2-50-UNV-L82765-S-CP187-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P311598
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-50-UNV-L82765-S-CP187-W2A-U-3000K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.187" POLYCARB SHEET
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4245.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 42.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P311598

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-S-CP187-W2A-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P311598

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-S-CP187-W2A-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		69
3	89	79	70	64	87	77	69	63	74	67	62		71	66	61		58
4	82	70	61	54	80	68	60	54	66	59	53		63	57	52		49
5	75	62	53	46	73	61	53	46	59	51	46		57	50	45		42
6	70	56	47	40	68	55	47	40	53	46	40		52	45	40		37
7	64	51	42	36	63	50	42	36	48	41	35		47	40	35		33
8	60	46	38	32	58	46	37	32	44	37	32		43	36	31		29
9	56	43	34	29	55	42	34	29	41	34	28		40	33	28		26
10	53	39	31	26	51	39	31	26	38	31	26		37	30	26		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2007	2007	2007
5°	2005	2000	2012
10°	1997	1997	2012
15°	1978	1987	2008
20°	1952	1971	2002
25°	1916	1952	1990
30°	1873	1929	1973
35°	1832	1898	1958
40°	1769	1866	1935
45°	1711	1829	1914
50°	1645	1795	1891
55°	1572	1762	1872
60°	1499	1734	1869
65°	1404	1704	1880
70°	1300	1713	1931
75°	1163	1745	2040
80°	941	1850	1995
85°	707	1624	1582



TEST NUMBER: P311598

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-S-CP187-W2A-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.2	3.3
10°-20°	403.4	9.5
20°-30°	606.4	14.3
30°-40°	722.3	17.0
40°-50°	739.3	17.4
50°-60°	665.6	15.7
60°-70°	522.7	12.3
70°-80°	339.2	8.0
80°-90°	104.9	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1151.0	27.1
0°-40°	1873.3	44.1
0°-60°	3278.2	77.2
0°-90°	4245.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4245.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1491	1491	1491	1491	1491	
5°	1485	1487	1480	1489	1490	141
15°	1420	1424	1427	1439	1441	400
25°	1290	1301	1315	1336	1340	594
35°	1115	1129	1156	1184	1192	696
45°	899	921	961	998	1006	693
55°	670	700	751	790	798	601
65°	441	475	535	580	591	439
75°	224	267	336	382	392	237
85°	46	85	105	102	102	55
90°	0	0	0	0	0	



TEST NUMBER: P311598

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-S-CP187-W2A-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1491.3	1491.3	1491.3	1491.3	1491.3
2.5°	1492.6	1492.6	1485.9	1492.6	1494.0
5°	1484.6	1487.3	1480.5	1488.6	1489.9
7.5°	1476.5	1476.5	1472.4	1480.5	1481.9
10°	1461.6	1463.0	1461.6	1471.1	1472.4
12.5°	1442.8	1445.5	1446.8	1456.2	1457.6
15°	1419.8	1423.9	1426.6	1438.7	1441.4
17.5°	1394.2	1398.3	1405.0	1418.5	1421.2
20°	1363.2	1368.6	1376.7	1394.2	1398.3
22.5°	1329.5	1334.9	1348.4	1364.5	1371.3
25°	1290.4	1301.2	1314.7	1336.2	1340.3
27.5°	1251.3	1260.7	1278.3	1301.2	1306.6
30°	1205.4	1220.3	1241.8	1264.8	1270.2
32.5°	1160.9	1175.8	1201.4	1225.7	1232.4
35°	1115.1	1128.6	1155.6	1183.9	1192.0
37.5°	1062.5	1080.0	1109.7	1138.0	1146.1
40°	1007.2	1028.8	1062.5	1092.2	1101.6
42.5°	954.6	977.6	1011.3	1043.6	1054.4
45°	899.4	920.9	961.4	997.8	1005.9
47.5°	842.7	867.0	910.1	946.6	960.0
50°	786.1	811.7	857.6	895.3	903.4
52.5°	729.5	756.4	805.0	845.4	849.5
55°	670.1	699.8	751.0	790.1	798.2
57.5°	616.2	641.8	697.1	737.6	747.0
60°	556.9	585.2	644.5	682.3	694.4
62.5°	500.2	529.9	591.9	629.7	640.5
65°	440.9	474.6	535.3	579.8	590.6
67.5°	389.7	422.0	486.8	529.9	540.7
70°	330.4	366.8	435.5	480.0	490.8
72.5°	279.1	316.9	385.6	428.8	445.0
75°	223.8	267.0	335.7	381.6	392.4
77.5°	169.9	219.8	289.9	325.0	325.0
80°	121.4	173.9	238.7	254.8	257.5
82.5°	79.6	130.8	176.6	175.3	175.3
85°	45.8	84.9	105.2	102.5	102.5
87.5°	17.5	35.1	37.8	37.8	36.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)