

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P310914

Luminaire Tested: **24FCZ2-50-UNV-L82765-CP125-W2A-U-3000K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P310914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-15)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-50-UNV-L82765-CP125-W2A-U-3000K
Description: 2'X4' TROFFER LED MODULE, RIBBED LENS, 0.125" POLYCARB SHEET
Light Source: (168) 3000K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4218.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.29 / 1.38
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 42.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P310914

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-CP125-W2A-U-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P310914

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-CP125-W2A-U-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	98	94	105	100	96	92	96	92	89		92	89	87		82
2	98	89	81	75	95	87	80	74	83	78	73		80	75	71		67
3	89	77	69	62	86	76	68	61	73	66	60		70	64	59		56
4	81	68	59	52	79	67	58	52	64	57	51		62	56	50		47
5	74	61	52	45	72	60	51	44	58	50	44		56	49	43		41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		36
7	64	50	41	34	62	49	40	34	47	39	34		46	39	34		31
8	59	45	37	31	57	45	36	30	43	36	30		42	35	30		28
9	55	41	33	27	54	41	33	27	40	32	27		39	32	27		25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	25		23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1872	1872	1872
5°	1875	1864	1875
10°	1864	1859	1874
15°	1848	1852	1875
20°	1825	1839	1874
25°	1797	1826	1872
30°	1763	1811	1870
35°	1729	1793	1871
40°	1689	1780	1883
45°	1648	1768	1899
50°	1599	1764	1927
55°	1559	1766	1966
60°	1499	1781	2034
65°	1430	1800	2107
70°	1354	1855	2224
75°	1208	1935	2430
80°	1030	2049	2483
85°	735	2030	2376



TEST NUMBER: P310914

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-CP125-W2A-U-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.7	3.1
10°-20°	376.4	8.9
20°-30°	568.6	13.5
30°-40°	685.3	16.2
40°-50°	719.4	17.1
50°-60°	673.0	16.0
60°-70°	555.8	13.2
70°-80°	378.7	9.0
80°-90°	129.2	3.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1076.6	25.5
0°-40°	1761.9	41.8
0°-60°	3154.3	74.8
0°-90°	4218.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4218.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1391	1391	1391	1391	1391	
5°	1388	1387	1380	1388	1388	132
15°	1327	1328	1330	1344	1346	374
25°	1210	1216	1230	1254	1261	557
35°	1052	1064	1092	1128	1139	658
45°	866	884	929	980	998	668
55°	665	691	753	814	838	593
65°	449	487	565	637	662	446
75°	232	286	372	442	467	248
85°	48	94	132	148	154	60
90°	0	0	0	0	0	



TEST NUMBER: P310914

CATALOG NUMBER: 24FCZ2-50-UNV-L82765-CP125-W2A-U-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1391.1	1391.1	1391.1	1391.1	1391.1
2.5°	1392.5	1391.1	1384.1	1391.1	1389.7
5°	1388.3	1386.9	1379.9	1388.3	1388.3
7.5°	1378.5	1378.5	1371.5	1381.3	1382.7
10°	1364.5	1364.5	1360.3	1371.5	1371.5
12.5°	1347.7	1347.7	1347.7	1358.9	1360.3
15°	1326.7	1328.1	1329.5	1343.5	1346.3
17.5°	1301.5	1304.3	1308.5	1325.3	1328.1
20°	1274.9	1277.7	1284.7	1304.3	1308.5
22.5°	1241.3	1248.3	1258.1	1280.5	1284.7
25°	1210.5	1216.1	1230.1	1253.9	1260.9
27.5°	1172.7	1181.1	1199.3	1224.5	1234.3
30°	1135.0	1143.4	1165.7	1195.1	1203.5
32.5°	1094.4	1107.0	1130.8	1161.5	1171.3
35°	1052.4	1063.6	1091.6	1128.0	1139.2
37.5°	1006.2	1021.6	1052.4	1091.6	1105.6
40°	961.4	978.2	1013.2	1055.2	1072.0
42.5°	916.6	933.4	972.6	1020.2	1037.0
45°	866.3	884.5	929.2	979.6	997.8
47.5°	815.9	838.3	887.3	940.4	960.0
50°	764.1	789.3	842.5	898.5	920.8
52.5°	717.9	741.7	797.7	857.9	878.9
55°	664.7	691.3	752.9	814.5	838.3
57.5°	610.2	639.6	705.3	772.5	796.3
60°	557.0	589.2	661.9	729.1	755.7
62.5°	505.2	537.4	613.0	682.9	709.5
65°	449.2	487.0	565.4	636.8	661.9
67.5°	396.0	436.6	519.2	589.2	614.4
70°	344.3	383.5	471.6	540.2	565.4
72.5°	288.3	333.1	421.2	492.6	519.2
75°	232.3	285.5	372.3	442.2	467.4
77.5°	180.5	235.1	321.9	379.3	391.8
80°	132.9	188.9	264.5	305.1	320.5
82.5°	85.4	141.3	201.5	230.9	243.5
85°	47.6	93.8	131.5	148.3	153.9
87.5°	19.6	40.6	53.2	60.2	60.2
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)