

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P311498

Luminaire Tested: **24FCZ2-45-UNV-L82765-S-CP125-W2A-U-2700K**

Issue Date: 3/3/2020

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Test Information

Test Method: LM-79-08
Report Number: P311498
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1805-783-1)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: 24FCZ2-45-UNV-L82765-S-CP125-W2A-U-2700K
Description: 2'X4' TROFFER LED MODULE, SMOOTH LENS, 0.125" POLYCARB SHEET
Light Source: (168) 2700K TUNABLE CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER
Luminaire Equipment:

<u>Sample No.</u>	<u>Condition</u>	<u>Description</u>
AS-5443-1	Good	WHITE TWIN R-EVOLVE FLOOD
AS-5443-2	Good	REFLECTOR
AS-5443-3	Good	DRIVER
AS-5443-4	Good	UPPER MODULE
AS-5443-5	Good	LENS
AS-5443-6	Good	DRIVER 2
AS-5443-7	Good	TRIM RING

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3904.0 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.26 / 1.35
Luminous Opening: Rectangular (W 2' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 37.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P311498

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-S-CP125-W2A-U-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P311498

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-S-CP125-W2A-U-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		69
3	89	79	70	64	87	77	69	63	74	67	62		71	66	61		58
4	82	70	61	54	80	68	60	54	66	59	53		63	57	52		49
5	75	62	53	46	73	61	53	46	59	51	46		57	50	45		42
6	70	56	47	40	68	55	47	40	53	46	40		52	45	40		37
7	64	51	42	36	63	50	42	36	48	41	35		47	40	35		33
8	60	46	38	32	58	46	37	32	44	37	32		43	36	31		29
9	56	43	34	29	55	42	34	29	41	34	28		40	33	28		26
10	53	39	31	26	51	39	31	26	38	31	26		37	30	26		24

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1845	1845	1845
5°	1844	1839	1851
10°	1837	1837	1850
15°	1819	1828	1846
20°	1795	1813	1841
25°	1762	1795	1830
30°	1722	1774	1815
35°	1684	1746	1801
40°	1627	1716	1779
45°	1574	1682	1760
50°	1513	1651	1739
55°	1446	1620	1722
60°	1378	1595	1718
65°	1291	1567	1729
70°	1195	1576	1776
75°	1070	1605	1876
80°	865	1701	1836
85°	651	1493	1454



TEST NUMBER: P311498

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-S-CP125-W2A-U-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.8	3.3
10°-20°	371.0	9.5
20°-30°	557.7	14.3
30°-40°	664.3	17.0
40°-50°	679.9	17.4
50°-60°	612.1	15.7
60°-70°	480.7	12.3
70°-80°	312.0	8.0
80°-90°	96.5	2.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1058.5	27.1
0°-40°	1722.9	44.1
0°-60°	3014.8	77.2
0°-90°	3904.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3904.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1365	1368	1362	1369	1370	130
15°	1306	1310	1312	1323	1326	368
25°	1187	1197	1209	1229	1233	547
35°	1026	1038	1063	1089	1096	640
45°	827	847	884	918	925	638
55°	616	644	691	727	734	553
65°	406	436	492	533	543	404
75°	206	246	309	351	361	218
85°	42	78	97	94	94	51
90°	0	0	0	0	0	



TEST NUMBER: P311498

CATALOG NUMBER: 24FCZ2-45-UNV-L82765-S-CP125-W2A-U-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.5	1371.5	1371.5	1371.5	1371.5
2.5°	1372.7	1372.7	1366.5	1372.7	1374.0
5°	1365.3	1367.8	1361.6	1369.0	1370.3
7.5°	1357.9	1357.9	1354.1	1361.6	1362.8
10°	1344.2	1345.5	1344.2	1352.9	1354.1
12.5°	1326.9	1329.3	1330.6	1339.3	1340.5
15°	1305.8	1309.5	1312.0	1323.1	1325.6
17.5°	1282.2	1285.9	1292.1	1304.5	1307.0
20°	1253.7	1258.7	1266.1	1282.2	1285.9
22.5°	1222.7	1227.7	1240.1	1254.9	1261.1
25°	1186.7	1196.7	1209.1	1228.9	1232.6
27.5°	1150.8	1159.5	1175.6	1196.7	1201.6
30°	1108.6	1122.2	1142.1	1163.2	1168.1
32.5°	1067.7	1081.3	1104.9	1127.2	1133.4
35°	1025.5	1037.9	1062.7	1088.8	1096.2
37.5°	977.2	993.3	1020.6	1046.6	1054.0
40°	926.3	946.2	977.2	1004.4	1013.1
42.5°	878.0	899.0	930.0	959.8	969.7
45°	827.1	847.0	884.2	917.6	925.1
47.5°	775.0	797.4	837.0	870.5	882.9
50°	723.0	746.5	788.7	823.4	830.8
52.5°	670.9	695.7	740.3	777.5	781.2
55°	616.3	643.6	690.7	726.7	734.1
57.5°	566.7	590.3	641.1	678.3	687.0
60°	512.1	538.2	592.7	627.5	638.6
62.5°	460.1	487.3	544.4	579.1	589.0
65°	405.5	436.5	492.3	533.2	543.1
67.5°	358.4	388.1	447.7	487.3	497.3
70°	303.8	337.3	400.5	441.5	451.4
72.5°	256.7	291.4	354.7	394.3	409.2
75°	205.8	245.5	308.8	350.9	360.9
77.5°	156.2	202.1	266.6	298.9	298.9
80°	111.6	160.0	219.5	234.4	236.9
82.5°	73.2	120.3	162.4	161.2	161.2
85°	42.2	78.1	96.7	94.2	94.2
87.5°	16.1	32.2	34.7	34.7	33.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)