

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P592622

Luminaire Tested: **HC415D010-HM40525850-41MDH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P592622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC415D010-HM40525850-41MDH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1508.0 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.91
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P592622

CATALOG NUMBER: HC415D010-HM40525850-41MDH

Luminous Intensity Polar Plot





TEST NUMBER: P592622

CATALOG NUMBER: HC415D010-HM40525850-41MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		82	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	76	70	66	84	76	70	65	74	69	65		73	68	64		71
7	81	71	65	61	80	71	65	61	69	64	60		68	63	60		67
8	77	67	61	56	76	66	60	56	65	60	56		64	59	56		63
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195231
5°	191148
10°	180646
15°	168713
20°	154298
25°	137784
30°	115708
35°	81387
40°	50221
45°	30073
50°	17712
55°	8817
60°	4539
65°	2977
70°	1839
75°	1477
80°	710
85°	1415



TEST NUMBER: P592622

CATALOG NUMBER: HC415D010-HM40525850-41MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	9.6
10°-20°	369.3	24.5
20°-30°	460.6	30.5
30°-40°	339.3	22.5
40°-50°	139.5	9.3
50°-60°	40.8	2.7
60°-70°	10.5	0.7
70°-80°	3.2	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	974.0	64.6
0°-40°	1313.3	87.1
0°-60°	1493.6	99.0
0°-90°	1508.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1508.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1583	
5°	1544	144
15°	1321	369
25°	1012	461
35°	540	339
45°	172	140
55°	41	41
65°	10	10
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P592622

CATALOG NUMBER: HC415D010-HM40525850-41MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1582.8
2.5°	1566.3
5°	1543.8
7.5°	1502.8
10°	1442.3
12.5°	1382.7
15°	1321.2
17.5°	1252.5
20°	1175.5
22.5°	1095.5
25°	1012.4
27.5°	920.1
30°	812.4
32.5°	682.1
35°	540.5
37.5°	415.5
40°	311.9
42.5°	230.8
45°	172.4
47.5°	127.2
50°	92.3
52.5°	63.6
55°	41.0
57.5°	24.7
60°	18.4
62.5°	13.3
65°	10.2
67.5°	7.2
70°	5.1
72.5°	4.1
75°	3.1
77.5°	2.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)