

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581712

Luminaire Tested: **HC6R15D010-HM60525827-62RMDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581712  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC6R15D010-HM60525827-62RMDC  
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1562.5 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581712

CATALOG NUMBER: HC6R15D010-HM60525827-62RMDC

### Luminous Intensity Polar Plot





TEST NUMBER: P581712

CATALOG NUMBER: HC6R15D010-HM60525827-62RMDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72472
5°	74064
10°	78511
15°	87753
20°	91883
25°	76607
30°	53622
35°	36112
40°	18592
45°	6458
50°	2874
55°	946
60°	439
65°	389
70°	305
75°	212
80°	316
85°	0



TEST NUMBER: P581712

CATALOG NUMBER: HC6R15D010-HM60525827-62RMDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	130.5	8.3
10°-20°	435.7	27.9
20°-30°	566.2	36.2
30°-40°	334.4	21.4
40°-50°	79.8	5.1
50°-60°	11.8	0.8
60°-70°	2.9	0.2
70°-80°	1.2	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1132.3	72.5
0°-40°	1466.8	93.9
0°-60°	1558.3	99.7
0°-90°	1562.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1562.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1322	
5°	1346	130
15°	1546	436
25°	1266	566
35°	540	334
45°	83	80
55°	10	12
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581712

CATALOG NUMBER: HC6R15D010-HM60525827-62RMDC

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1322.0
2.5°	1325.0
5°	1345.9
7.5°	1372.7
10°	1410.4
12.5°	1469.8
15°	1546.2
17.5°	1597.9
20°	1575.0
22.5°	1460.0
25°	1266.5
27.5°	1045.3
30°	847.1
32.5°	685.3
35°	539.6
37.5°	396.7
40°	259.8
42.5°	141.9
45°	83.3
47.5°	51.5
50°	33.7
52.5°	19.9
55°	9.9
57.5°	5.0
60°	4.0
62.5°	4.0
65°	3.0
67.5°	1.9
70°	1.9
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)