

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581733

Luminaire Tested: **HC615D010-HM60525835-61MDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P581733  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC615D010-HM60525835-61MDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1496.2 lumens  
Efficiency: N/A  
Efficacy: 106.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P581733

CATALOG NUMBER: HC615D010-HM60525835-61MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P581733

CATALOG NUMBER: HC615D010-HM60525835-61MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	55703
5°	55492
10°	54569
15°	53604
20°	51752
25°	49073
30°	44640
35°	35663
40°	23802
45°	16963
50°	14132
55°	12320
60°	11633
65°	10948
70°	10082
75°	9404
80°	8555
85°	7485



TEST NUMBER: P581733

CATALOG NUMBER: HC615D010-HM60525835-61MDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.4	6.4
10°-20°	265.2	17.7
20°-30°	370.6	24.8
30°-40°	326.5	21.8
40°-50°	176.4	11.8
50°-60°	117.9	7.9
60°-70°	83.6	5.6
70°-80°	47.0	3.1
80°-90°	13.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	731.2	48.9
0°-40°	1057.7	70.7
0°-60°	1352.0	90.4
0°-90°	1496.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1496.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1016	
5°	1008	95
15°	944	265
25°	811	371
35°	533	326
45°	219	176
55°	129	118
65°	84	84
75°	44	47
85°	12	14
90°	0	



TEST NUMBER: P581733

CATALOG NUMBER: HC615D010-HM60525835-61MDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1016.1
2.5°	1010.6
5°	1008.4
7.5°	998.7
10°	980.3
12.5°	962.9
15°	944.5
17.5°	919.6
20°	887.1
22.5°	851.4
25°	811.3
27.5°	764.8
30°	705.2
32.5°	631.5
35°	532.9
37.5°	425.7
40°	332.6
42.5°	262.2
45°	218.8
47.5°	189.5
50°	165.7
52.5°	146.2
55°	128.9
57.5°	117.0
60°	106.1
62.5°	95.3
65°	84.4
67.5°	73.7
70°	62.9
72.5°	53.1
75°	44.4
77.5°	35.8
80°	27.1
82.5°	19.5
85°	11.9
87.5°	5.4
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)