

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581850

Luminaire Tested: **HC620D010-HM60525827-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581850
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC620D010-HM60525827-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1979.7 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581850

CATALOG NUMBER: HC620D010-HM60525827-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P581850

CATALOG NUMBER: HC620D010-HM60525827-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	87	83	98	91	86	82	89	84	81		86	83	80		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	83	73	67	62	82	73	66	62	71	65	61		70	65	61		68
7	79	68	62	57	77	68	61	57	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	59	53	48	69	59	53	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		53	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77532
5°	78048
10°	78951
15°	80568
20°	81020
25°	78494
30°	71213
35°	57902
40°	38429
45°	21390
50°	11991
55°	6662
60°	3673
65°	2776
70°	1923
75°	1419
80°	852
85°	881



TEST NUMBER: P581850

CATALOG NUMBER: HC620D010-HM60525827-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	6.8
10°-20°	400.3	20.2
20°-30°	590.0	29.8
30°-40°	527.7	26.7
40°-50°	228.9	11.6
50°-60°	67.3	3.4
60°-70°	21.4	1.1
70°-80°	7.6	0.4
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1125.6	56.9
0°-40°	1653.3	83.5
0°-60°	1949.5	98.5
0°-90°	1979.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1979.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1414	
5°	1418	135
15°	1420	400
25°	1298	590
35°	865	528
45°	276	229
55°	70	67
65°	21	21
75°	7	8
85°	1	1
90°	0	



TEST NUMBER: P581850

CATALOG NUMBER: HC620D010-HM60525827-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1414.3
2.5°	1410.2
5°	1418.3
7.5°	1421.0
10°	1418.3
12.5°	1418.3
15°	1419.6
17.5°	1411.6
20°	1388.8
22.5°	1350.0
25°	1297.7
27.5°	1224.1
30°	1125.0
32.5°	1007.1
35°	865.2
37.5°	703.1
40°	537.0
42.5°	392.4
45°	275.9
47.5°	196.9
50°	140.6
52.5°	100.5
55°	69.7
57.5°	46.9
60°	33.5
62.5°	26.7
65°	21.4
67.5°	16.1
70°	12.0
72.5°	9.4
75°	6.7
77.5°	5.3
80°	2.7
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)