

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581929

Luminaire Tested: **HC620D010-HM60525930-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC620D010-HM60525930-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1946.1 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581929

CATALOG NUMBER: HC620D010-HM60525930-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P581929

CATALOG NUMBER: HC620D010-HM60525930-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	92416
5°	93853
10°	99202
15°	110455
20°	114547
25°	93985
30°	65852
35°	44925
40°	23401
45°	8233
50°	3684
55°	1176
60°	669
65°	480
70°	401
75°	254
80°	0
85°	0



TEST NUMBER: P581929

CATALOG NUMBER: HC620D010-HM60525930-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.2	8.5
10°-20°	547.3	28.1
20°-30°	696.9	35.8
30°-40°	415.3	21.3
40°-50°	100.7	5.2
50°-60°	15.4	0.8
60°-70°	3.8	0.2
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1409.5	72.4
0°-40°	1824.8	93.8
0°-60°	1941.0	99.7
0°-90°	1946.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1946.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1686	
5°	1706	165
15°	1946	547
25°	1554	697
35°	671	415
45°	106	101
55°	12	15
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581929

CATALOG NUMBER: HC620D010-HM60525930-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	1685.8
2.5°	1685.8
5°	1705.5
7.5°	1736.4
10°	1782.1
12.5°	1853.6
15°	1946.2
17.5°	2004.2
20°	1963.5
22.5°	1806.7
25°	1553.8
27.5°	1274.9
30°	1040.3
32.5°	850.3
35°	671.3
37.5°	494.9
40°	327.0
42.5°	176.5
45°	106.2
47.5°	66.6
50°	43.2
52.5°	25.9
55°	12.3
57.5°	7.4
60°	6.1
62.5°	5.0
65°	3.7
67.5°	2.5
70°	2.5
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)