

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582002

Luminaire Tested: **HC625D010-HM60525830-61MDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582002  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC625D010-HM60525830-61MDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2529.5 lumens  
Efficiency: N/A  
Efficacy: 94.4 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582002

CATALOG NUMBER: HC625D010-HM60525830-61MDH

### Luminous Intensity Polar Plot





TEST NUMBER: P582002

CATALOG NUMBER: HC625D010-HM60525830-61MDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126689
5°	126585
10°	125265
15°	122748
20°	116274
25°	105000
30°	89197
35°	65859
40°	38078
45°	20211
50°	11420
55°	5974
60°	3914
65°	2776
70°	2004
75°	1504
80°	1137
85°	1132



TEST NUMBER: P582002

CATALOG NUMBER: HC625D010-HM60525830-61MDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	218.0	8.6
10°-20°	604.9	23.9
20°-30°	789.5	31.2
30°-40°	603.3	23.9
40°-50°	218.4	8.6
50°-60°	63.4	2.5
60°-70°	22.7	0.9
70°-80°	7.8	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1612.4	63.7
0°-40°	2215.7	87.6
0°-60°	2497.6	98.7
0°-90°	2529.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2529.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2311	
5°	2300	218
15°	2163	605
25°	1736	790
35°	984	603
45°	261	218
55°	62	63
65°	21	23
75°	7	8
85°	2	1
90°	0	



TEST NUMBER: P582002

CATALOG NUMBER: HC625D010-HM60525830-61MDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2311.0
2.5°	2300.3
5°	2300.3
7.5°	2284.2
10°	2250.3
12.5°	2211.0
15°	2162.8
17.5°	2091.4
20°	1993.1
22.5°	1871.6
25°	1735.9
27.5°	1582.3
30°	1409.1
32.5°	1214.4
35°	984.1
37.5°	742.9
40°	532.1
42.5°	367.9
45°	260.7
47.5°	187.6
50°	133.9
52.5°	94.6
55°	62.5
57.5°	44.6
60°	35.7
62.5°	28.6
65°	21.4
67.5°	17.9
70°	12.5
72.5°	8.9
75°	7.1
77.5°	5.4
80°	3.6
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)