

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593183

Luminaire Tested: **HC6R25D010-HM60525950-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593183
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R25D010-HM60525950-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2570.7 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593183

CATALOG NUMBER: HC6R25D010-HM60525950-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P593183

CATALOG NUMBER: HC6R25D010-HM60525950-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	91		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	60	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119239
5°	121852
10°	129161
15°	144371
20°	151166
25°	126038
30°	88210
35°	59401
40°	30593
45°	10629
50°	4733
55°	1558
60°	713
65°	636
70°	529
75°	339
80°	505
85°	0



TEST NUMBER: P593183

CATALOG NUMBER: HC6R25D010-HM60525950-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.6	8.3
10°-20°	716.7	27.9
20°-30°	931.5	36.2
30°-40°	550.2	21.4
40°-50°	131.3	5.1
50°-60°	19.3	0.8
60°-70°	4.8	0.2
70°-80°	1.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1862.9	72.5
0°-40°	2413.1	93.9
0°-60°	2563.7	99.7
0°-90°	2570.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2570.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2175	
5°	2214	215
15°	2544	717
25°	2084	932
35°	888	550
45°	137	131
55°	16	19
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P593183

CATALOG NUMBER: HC6R25D010-HM60525950-62RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2175.1
2.5°	2180.0
5°	2214.3
7.5°	2258.3
10°	2320.3
12.5°	2418.2
15°	2543.8
17.5°	2628.7
20°	2591.2
22.5°	2401.9
25°	2083.7
27.5°	1719.9
30°	1393.5
32.5°	1127.6
35°	887.6
37.5°	652.7
40°	427.5
42.5°	233.3
45°	137.1
47.5°	84.8
50°	55.5
52.5°	32.6
55°	16.3
57.5°	8.1
60°	6.5
62.5°	6.5
65°	4.9
67.5°	3.3
70°	3.3
72.5°	1.6
75°	1.6
77.5°	1.6
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)