

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582234

Luminaire Tested: **HC6R30D010-HM63040930-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582234
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R30D010-HM63040930-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3253.9 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582234

CATALOG NUMBER: HC6R30D010-HM63040930-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P582234

CATALOG NUMBER: HC6R30D010-HM63040930-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	91		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	60	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150925
5°	154231
10°	163485
15°	182742
20°	191344
25°	159541
30°	111656
35°	75195
40°	38723
45°	13451
50°	5996
55°	1978
60°	899
65°	804
70°	673
75°	424
80°	631
85°	0



TEST NUMBER: P582234

CATALOG NUMBER: HC6R30D010-HM63040930-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.7	8.3
10°-20°	907.2	27.9
20°-30°	1179.1	36.2
30°-40°	696.5	21.4
40°-50°	166.1	5.1
50°-60°	24.5	0.8
60°-70°	6.1	0.2
70°-80°	2.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2358.0	72.5
0°-40°	3054.5	93.9
0°-60°	3245.1	99.7
0°-90°	3253.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3253.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2753	
5°	2803	272
15°	3220	907
25°	2638	1179
35°	1124	696
45°	174	166
55°	21	24
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582234

CATALOG NUMBER: HC6R30D010-HM63040930-62RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2753.1
2.5°	2759.4
5°	2802.7
7.5°	2858.5
10°	2936.9
12.5°	3061.0
15°	3219.9
17.5°	3327.4
20°	3279.9
22.5°	3040.3
25°	2637.6
27.5°	2176.9
30°	1763.9
32.5°	1427.2
35°	1123.6
37.5°	826.1
40°	541.1
42.5°	295.3
45°	173.5
47.5°	107.4
50°	70.3
52.5°	41.3
55°	20.7
57.5°	10.3
60°	8.2
62.5°	8.2
65°	6.2
67.5°	4.2
70°	4.2
72.5°	2.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)