

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582256

Luminaire Tested: **HC630D010-HM63040940-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC630D010-HM63040940-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3180.5 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582256

CATALOG NUMBER: HC630D010-HM63040940-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P582256

CATALOG NUMBER: HC630D010-HM63040940-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	108	106	111	109	107	105		105	103	101			101	100	98			98
2	108	103	99	96	106	102	98	95		98	96	93			96	93	91			93
3	103	97	92	88	101	95	91	87		93	89	86			90	87	84			88
4	98	90	85	81	96	89	84	80		87	83	79			85	81	79			83
5	93	85	79	75	91	84	78	75		82	77	74			80	76	73			79
6	88	80	74	70	87	79	73	69		77	73	69			76	72	68			75
7	84	75	69	65	83	74	69	65		73	68	64			72	67	64			71
8	80	71	65	61	79	70	65	61		69	64	60			68	64	60			67
9	76	67	61	57	75	66	61	57		65	60	57			65	60	57			64
10	73	63	58	54	72	63	57	54		62	57	54			61	57	53			61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	189935
5°	190314
10°	193450
15°	194859
20°	178130
25°	139968
30°	102459
35°	72678
40°	34379
45°	13118
50°	5885
55°	1606
60°	691
65°	545
70°	337
75°	445
80°	0
85°	0



TEST NUMBER: P582256

CATALOG NUMBER: HC630D010-HM63040940-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.8	10.4
10°-20°	949.0	29.8
20°-30°	1055.6	33.2
30°-40°	659.4	20.7
40°-50°	156.7	4.9
50°-60°	22.4	0.7
60°-70°	4.7	0.1
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2335.4	73.4
0°-40°	2994.8	94.2
0°-60°	3173.9	99.8
0°-90°	3180.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3180.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3465	
5°	3458	331
15°	3433	949
25°	2314	1056
35°	1086	659
45°	169	157
55°	17	22
65°	4	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582256

CATALOG NUMBER: HC630D010-HM63040940-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3464.7
2.5°	3450.1
5°	3458.4
7.5°	3471.0
10°	3475.2
12.5°	3473.1
15°	3433.4
17.5°	3299.7
20°	3053.4
22.5°	2706.6
25°	2314.0
27.5°	1938.1
30°	1618.6
32.5°	1353.3
35°	1086.0
37.5°	797.8
40°	480.4
42.5°	277.8
45°	169.2
47.5°	108.6
50°	69.0
52.5°	39.7
55°	16.8
57.5°	8.3
60°	6.3
62.5°	6.3
65°	4.2
67.5°	4.2
70°	2.1
72.5°	2.1
75°	2.1
77.5°	2.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)