

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582263

Luminaire Tested: **HC630D010-HM63040940-61WDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC630D010-HM63040940-61WDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3368.3 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582263

CATALOG NUMBER: HC630D010-HM63040940-61WDC

Luminous Intensity Polar Plot





TEST NUMBER: P582263

CATALOG NUMBER: HC630D010-HM63040940-61WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	110	108	105	111	108	106	103		104	102	100			100	99	97			97
2	107	102	97	94	105	100	96	93		97	94	91			94	91	89			91
3	101	94	89	85	99	93	88	84		90	86	82			88	84	81			85
4	95	87	81	77	93	86	80	76		84	79	75			82	78	74			80
5	90	81	75	70	88	80	74	70		78	73	69			76	72	68			75
6	85	75	69	64	83	74	68	64		73	67	63			71	67	63			70
7	80	70	63	59	79	69	63	59		68	62	58			67	62	58			66
8	76	65	59	54	74	65	59	54		64	58	54			62	57	54			61
9	71	61	55	50	70	60	54	50		60	54	50			59	53	50			58
10	68	57	51	47	67	57	51	47		56	50	46			55	50	46			54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119420
5°	121021
10°	125554
15°	136544
20°	152666
25°	160691
30°	141458
35°	98123
40°	58588
45°	27848
50°	10507
55°	4387
60°	1371
65°	1077
70°	673
75°	445
80°	663
85°	0



TEST NUMBER: P582263

CATALOG NUMBER: HC630D010-HM63040940-61WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	211.7	6.3
10°-20°	690.9	20.5
20°-30°	1183.8	35.1
30°-40°	919.4	27.3
40°-50°	303.9	9.0
50°-60°	46.6	1.4
60°-70°	8.2	0.2
70°-80°	3.0	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2086.3	61.9
0°-40°	3005.7	89.2
0°-60°	3356.2	99.6
0°-90°	3368.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3368.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2178	
5°	2199	212
15°	2406	691
25°	2657	1184
35°	1466	919
45°	359	304
55°	46	47
65°	8	8
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P582263

CATALOG NUMBER: HC630D010-HM63040940-61WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2178.4
2.5°	2176.2
5°	2199.2
7.5°	2224.3
10°	2255.5
12.5°	2318.2
15°	2405.9
17.5°	2512.5
20°	2616.9
22.5°	2677.5
25°	2656.6
27.5°	2512.5
30°	2234.7
32.5°	1860.9
35°	1466.2
37.5°	1113.1
40°	818.7
42.5°	578.6
45°	359.2
47.5°	200.5
50°	123.2
52.5°	75.1
55°	45.9
57.5°	22.9
60°	12.5
62.5°	10.5
65°	8.3
67.5°	6.3
70°	4.2
72.5°	4.2
75°	2.1
77.5°	2.1
80°	2.1
82.5°	2.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)