

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582275

Luminaire Tested: **HC635D010-HM63040827-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582275
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC635D010-HM63040827-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3531.9 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582275

CATALOG NUMBER: HC635D010-HM63040827-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P582275

CATALOG NUMBER: HC635D010-HM63040827-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	70	64	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	56	64	59	55		63	59	55		62
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216200
5°	215281
10°	210183
15°	199524
20°	177839
25°	149809
30°	119354
35°	85153
40°	45793
45°	19614
50°	8921
55°	3259
60°	1601
65°	1258
70°	1186
75°	530
80°	789
85°	0



TEST NUMBER: P582275

CATALOG NUMBER: HC635D010-HM63040827-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.3	10.5
10°-20°	974.5	27.6
20°-30°	1128.7	32.0
30°-40°	780.4	22.1
40°-50°	225.4	6.4
50°-60°	38.8	1.1
60°-70°	9.9	0.3
70°-80°	3.9	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2472.4	70.0
0°-40°	3252.8	92.1
0°-60°	3517.0	99.6
0°-90°	3531.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3531.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3944	
5°	3912	369
15°	3516	974
25°	2477	1129
35°	1272	780
45°	253	225
55°	34	39
65°	10	10
75°	2	4
85°	0	1
90°	0	



TEST NUMBER: P582275

CATALOG NUMBER: HC635D010-HM63040827-61NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3943.8
2.5°	3926.7
5°	3912.1
7.5°	3868.3
10°	3775.8
12.5°	3663.9
15°	3515.6
17.5°	3306.3
20°	3048.4
22.5°	2763.8
25°	2476.7
27.5°	2182.3
30°	1885.5
32.5°	1588.6
35°	1272.4
37.5°	944.0
40°	639.9
42.5°	403.9
45°	253.0
47.5°	163.0
50°	104.6
52.5°	63.3
55°	34.1
57.5°	19.5
60°	14.6
62.5°	12.1
65°	9.7
67.5°	7.4
70°	7.4
72.5°	4.9
75°	2.5
77.5°	2.5
80°	2.5
82.5°	2.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)