

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581717

Luminaire Tested: **HC615D010-HM60525830-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581717
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC615D010-HM60525830-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1548.2 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581717

CATALOG NUMBER: HC615D010-HM60525830-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P581717

CATALOG NUMBER: HC615D010-HM60525830-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	70	64	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	56	64	59	55		63	59	55		62
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94779
5°	94376
10°	92144
15°	87469
20°	77958
25°	65671
30°	52325
35°	37336
40°	20073
45°	8598
50°	3915
55°	1434
60°	702
65°	558
70°	513
75°	212
80°	316
85°	0



TEST NUMBER: P581717

CATALOG NUMBER: HC615D010-HM60525830-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.9	10.5
10°-20°	427.2	27.6
20°-30°	494.8	32.0
30°-40°	342.1	22.1
40°-50°	98.8	6.4
50°-60°	17.0	1.1
60°-70°	4.3	0.3
70°-80°	1.7	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1083.9	70.0
0°-40°	1426.0	92.1
0°-60°	1541.8	99.6
0°-90°	1548.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1548.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1729	
5°	1715	162
15°	1541	427
25°	1086	495
35°	558	342
45°	111	99
55°	15	17
65°	4	4
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P581717

CATALOG NUMBER: HC615D010-HM60525830-61NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1728.9
2.5°	1721.5
5°	1715.0
7.5°	1695.8
10°	1655.3
12.5°	1606.3
15°	1541.2
17.5°	1449.5
20°	1336.3
22.5°	1211.6
25°	1085.7
27.5°	956.7
30°	826.6
32.5°	696.4
35°	557.9
37.5°	413.8
40°	280.5
42.5°	177.1
45°	110.9
47.5°	71.5
50°	45.9
52.5°	27.7
55°	15.0
57.5°	8.5
60°	6.4
62.5°	5.3
65°	4.3
67.5°	3.2
70°	3.2
72.5°	2.2
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)