

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582846

Luminaire Tested: **HC6R50D010-HM64560940-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R50D010-HM64560940-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5276.1 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582846

CATALOG NUMBER: HC6R50D010-HM64560940-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P582846

CATALOG NUMBER: HC6R50D010-HM64560940-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	91		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	60	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	244728
5°	250087
10°	265098
15°	296318
20°	310255
25°	258680
30°	181041
35°	121920
40°	62796
45°	21808
50°	9705
55°	3202
60°	1458
65°	1297
70°	1074
75°	699
80°	1042
85°	0



TEST NUMBER: P582846

CATALOG NUMBER: HC6R50D010-HM64560940-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	440.5	8.3
10°-20°	1471.1	27.9
20°-30°	1911.8	36.2
30°-40°	1129.3	21.4
40°-50°	269.4	5.1
50°-60°	39.7	0.8
60°-70°	9.9	0.2
70°-80°	3.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3823.4	72.5
0°-40°	4952.7	93.9
0°-60°	5261.8	99.7
0°-90°	5276.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5276.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4464	
5°	4545	440
15°	5221	1471
25°	4277	1912
35°	1822	1129
45°	281	269
55°	34	40
65°	10	10
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P582846

CATALOG NUMBER: HC6R50D010-HM64560940-62RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4464.2
2.5°	4474.2
5°	4544.6
7.5°	4635.0
10°	4762.3
12.5°	4963.2
15°	5221.1
17.5°	5395.3
20°	5318.2
22.5°	4929.7
25°	4276.6
27.5°	3529.9
30°	2860.0
32.5°	2314.2
35°	1821.8
37.5°	1339.6
40°	877.5
42.5°	478.9
45°	281.3
47.5°	174.2
50°	113.8
52.5°	67.0
55°	33.5
57.5°	16.8
60°	13.3
62.5°	13.3
65°	10.0
67.5°	6.7
70°	6.7
72.5°	3.3
75°	3.3
77.5°	3.3
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)