

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581831

Luminaire Tested: **HC615D010-HM60525940-61WDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC615D010-HM60525940-61WDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1571.6 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581831

CATALOG NUMBER: HC615D010-HM60525940-61WDC

Luminous Intensity Polar Plot





TEST NUMBER: P581831

CATALOG NUMBER: HC615D010-HM60525940-61WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	103		104	102	100		100	99	97		97	96	94
2	107	102	97	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	82		88	84	81		85	82	80
4	95	87	81	77		93	86	80	76		84	79	75		82	78	74		80	76	74
5	90	81	75	70		88	80	74	70		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	63	59		79	69	63	59		68	62	58		67	62	58		66	61	58
8	76	65	59	54		74	65	59	54		64	58	54		62	57	54		61	57	53
9	71	61	55	50		70	60	54	50		60	54	50		59	53	50		58	53	50
10	68	57	51	47		67	57	51	47		56	50	46		55	50	46		54	50	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55719
5°	56471
10°	58583
15°	63706
20°	71231
25°	74974
30°	65997
35°	45782
40°	27337
45°	12994
50°	4904
55°	2055
60°	647
65°	506
70°	305
75°	212
80°	316
85°	0



TEST NUMBER: P581831

CATALOG NUMBER: HC615D010-HM60525940-61WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.8	6.3
10°-20°	322.3	20.5
20°-30°	552.3	35.1
30°-40°	429.0	27.3
40°-50°	141.8	9.0
50°-60°	21.8	1.4
60°-70°	3.9	0.2
70°-80°	1.4	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	973.4	61.9
0°-40°	1402.4	89.2
0°-60°	1566.0	99.6
0°-90°	1571.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1571.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1016	
5°	1026	99
15°	1122	322
25°	1240	552
35°	684	429
45°	168	142
55°	22	22
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581831

CATALOG NUMBER: HC615D010-HM60525940-61WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	1016.4
2.5°	1015.4
5°	1026.2
7.5°	1037.8
10°	1052.4
12.5°	1081.7
15°	1122.5
17.5°	1172.2
20°	1221.0
22.5°	1249.3
25°	1239.5
27.5°	1172.2
30°	1042.6
32.5°	868.3
35°	684.1
37.5°	519.4
40°	382.0
42.5°	269.9
45°	167.6
47.5°	93.5
50°	57.5
52.5°	35.1
55°	21.5
57.5°	10.7
60°	5.9
62.5°	4.9
65°	3.9
67.5°	3.0
70°	1.9
72.5°	1.9
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)