

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583119

Luminaire Tested: **HC655D010-HM64560940-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC655D010-HM64560940-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4842.6 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583119

CATALOG NUMBER: HC655D010-HM64560940-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P583119

CATALOG NUMBER: HC655D010-HM64560940-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	108	104	101		109	105	102	100		101	99	96		97	95	94		94	92	91
2	104	97	92	87		101	95	90	86		92	88	84		89	85	82		86	83	81
3	97	88	82	76		94	87	81	76		84	79	75		81	77	73		79	75	72
4	90	80	73	68		88	79	73	67		77	71	67		75	70	66		73	68	65
5	84	74	66	61		82	73	66	61		71	65	60		69	64	59		67	63	59
6	79	68	61	55		77	67	60	55		65	59	55		64	58	54		62	58	54
7	74	63	55	50		73	62	55	50		61	54	50		59	54	50		58	53	49
8	70	58	51	46		69	58	51	46		57	50	46		55	50	46		54	49	45
9	66	54	47	43		65	54	47	42		53	47	42		52	46	42		51	46	42
10	62	51	44	39		61	50	44	39		49	43	39		49	43	39		48	43	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	180271
5°	179611
10°	176611
15°	173497
20°	167507
25°	158828
30°	144465
35°	115429
40°	77023
45°	54897
50°	45747
55°	39874
60°	37661
65°	35464
70°	32602
75°	30437
80°	27687
85°	24279



TEST NUMBER: P583119

CATALOG NUMBER: HC655D010-HM64560940-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	308.7	6.4
10°-20°	858.4	17.7
20°-30°	1199.5	24.8
30°-40°	1056.6	21.8
40°-50°	570.8	11.8
50°-60°	381.7	7.9
60°-70°	270.5	5.6
70°-80°	152.1	3.1
80°-90°	44.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2366.5	48.9
0°-40°	3423.1	70.7
0°-60°	4375.6	90.4
0°-90°	4842.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4842.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3288	
5°	3264	309
15°	3057	858
25°	2626	1199
35°	1725	1057
45°	708	571
55°	417	382
65°	273	271
75°	144	152
85°	39	44
90°	0	



TEST NUMBER: P583119

CATALOG NUMBER: HC655D010-HM64560940-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3288.4
2.5°	3270.9
5°	3263.9
7.5°	3232.3
10°	3172.7
12.5°	3116.6
15°	3057.0
17.5°	2976.4
20°	2871.3
22.5°	2755.6
25°	2625.8
27.5°	2475.1
30°	2282.2
32.5°	2043.9
35°	1724.8
37.5°	1377.7
40°	1076.3
42.5°	848.4
45°	708.1
47.5°	613.5
50°	536.4
52.5°	473.3
55°	417.2
57.5°	378.7
60°	343.5
62.5°	308.5
65°	273.4
67.5°	238.4
70°	203.4
72.5°	171.8
75°	143.7
77.5°	115.7
80°	87.7
82.5°	63.1
85°	38.6
87.5°	17.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)