

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P581932

Luminaire Tested: **HC620D010-HM60525930-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P581932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC620D010-HM60525930-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1879.4 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P581932

CATALOG NUMBER: HC620D010-HM60525930-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P581932

CATALOG NUMBER: HC620D010-HM60525930-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	107	105		105	103	101		101	100	98		98	97	96
2	108	103	99	96		106	102	98	95		98	96	93		96	93	91		93	91	89
3	103	97	92	88		101	95	91	87		93	89	86		90	87	84		88	85	83
4	98	90	85	81		96	89	84	80		87	83	79		85	81	79		83	80	78
5	93	85	79	75		91	84	79	75		82	77	74		80	76	73		79	75	73
6	88	80	74	70		87	79	73	69		77	73	69		76	72	68		75	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	70	65	61		69	64	60		68	64	60		67	63	60
9	76	67	61	57		75	66	61	57		65	60	57		65	60	57		64	60	56
10	73	63	58	54		72	63	57	54		62	57	54		61	57	53		61	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112239
5°	112469
10°	114321
15°	115154
20°	105260
25°	82710
30°	60547
35°	42945
40°	20309
45°	7745
50°	3471
55°	946
60°	406
65°	324
70°	192
75°	254
80°	0
85°	0



TEST NUMBER: P581932

CATALOG NUMBER: HC620D010-HM60525930-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.5	10.4
10°-20°	560.8	29.8
20°-30°	623.8	33.2
30°-40°	389.7	20.7
40°-50°	92.6	4.9
50°-60°	13.3	0.7
60°-70°	2.8	0.1
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1380.1	73.4
0°-40°	1769.7	94.2
0°-60°	1875.6	99.8
0°-90°	1879.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1879.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2047	
5°	2044	196
15°	2029	561
25°	1367	624
35°	642	390
45°	100	93
55°	10	13
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P581932

CATALOG NUMBER: HC620D010-HM60525930-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2047.4
2.5°	2038.8
5°	2043.8
7.5°	2051.2
10°	2053.7
12.5°	2052.4
15°	2029.0
17.5°	1950.0
20°	1804.3
22.5°	1599.5
25°	1367.4
27.5°	1145.3
30°	956.5
32.5°	799.8
35°	641.7
37.5°	471.4
40°	283.8
42.5°	164.2
45°	99.9
47.5°	64.1
50°	40.7
52.5°	23.5
55°	9.9
57.5°	5.0
60°	3.7
62.5°	3.7
65°	2.5
67.5°	2.5
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)