

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583228

Luminaire Tested: **HC660D010-HM64560930-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583228
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC660D010-HM64560930-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5335.0 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583228

CATALOG NUMBER: HC660D010-HM64560930-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P583228

CATALOG NUMBER: HC660D010-HM64560930-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98
2	108	103	99	96	106	102	98	95	98	96	93		96	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	79		83
5	93	85	79	75	91	84	79	75	82	77	74		80	76	73		79
6	88	80	74	70	87	79	73	69	77	73	69		76	72	68		75
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318609
5°	319254
10°	324504
15°	326875
20°	298798
25°	234788
30°	171868
35°	121920
40°	57665
45°	22002
50°	9859
55°	2686
60°	1151
65°	908
70°	561
75°	741
80°	0
85°	0



TEST NUMBER: P583228

CATALOG NUMBER: HC660D010-HM64560930-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	555.0	10.4
10°-20°	1591.9	29.8
20°-30°	1770.6	33.2
30°-40°	1106.1	20.7
40°-50°	262.8	4.9
50°-60°	37.6	0.7
60°-70°	7.8	0.1
70°-80°	3.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3917.5	73.4
0°-40°	5023.6	94.2
0°-60°	5324.0	99.8
0°-90°	5335.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5335.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5812	
5°	5802	555
15°	5760	1592
25°	3882	1771
35°	1822	1106
45°	284	263
55°	28	38
65°	7	8
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P583228

CATALOG NUMBER: HC660D010-HM64560930-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	5811.9
2.5°	5787.4
5°	5801.5
7.5°	5822.5
10°	5829.5
12.5°	5826.0
15°	5759.5
17.5°	5535.2
20°	5121.8
22.5°	4540.2
25°	3881.6
27.5°	3251.0
30°	2715.1
32.5°	2270.1
35°	1821.8
37.5°	1338.2
40°	805.8
42.5°	465.9
45°	283.8
47.5°	182.2
50°	115.6
52.5°	66.5
55°	28.1
57.5°	14.0
60°	10.5
62.5°	10.5
65°	7.0
67.5°	7.0
70°	3.5
72.5°	3.5
75°	3.5
77.5°	3.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)