

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583243

Luminaire Tested: **HC660D010-HM64560935-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC660D010-HM64560935-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5589.1 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583243

CATALOG NUMBER: HC660D010-HM64560935-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P583243

CATALOG NUMBER: HC660D010-HM64560935-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	108	106	111	109	106	104		105	103	101			101	99	98			97
2	108	103	99	96	106	101	98	95		98	95	93			95	93	91			92
3	102	96	91	87	100	95	90	86		92	88	85			90	86	84			87
4	97	90	84	80	95	89	83	79		86	82	79			84	81	78			83
5	92	84	78	74	91	83	78	73		81	76	73			80	75	72			78
6	88	79	73	68	86	78	72	68		76	71	68			75	71	67			74
7	83	74	68	64	82	73	68	63		72	67	63			71	66	63			70
8	79	70	63	59	78	69	63	59		68	63	59			67	62	59			66
9	75	66	60	56	74	65	59	55		64	59	55			63	58	55			62
10	72	62	56	52	71	61	56	52		61	55	52			60	55	52			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265417
5°	269546
10°	284898
15°	317221
20°	328970
25°	269913
30°	189137
35°	129034
40°	67212
45°	23638
50°	10584
55°	3393
60°	1941
65°	1375
70°	1138
75°	741
80°	0
85°	0



TEST NUMBER: P583243

CATALOG NUMBER: HC660D010-HM64560935-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	474.5	8.5
10°-20°	1571.9	28.1
20°-30°	2001.5	35.8
30°-40°	1192.9	21.3
40°-50°	289.3	5.2
50°-60°	44.4	0.8
60°-70°	10.9	0.2
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4047.9	72.4
0°-40°	5240.8	93.8
0°-60°	5574.5	99.7
0°-90°	5589.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5589.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4842	
5°	4898	474
15°	5589	1572
25°	4462	2002
35°	1928	1193
45°	305	289
55°	36	44
65°	11	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P583243

CATALOG NUMBER: HC660D010-HM64560935-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4841.6
2.5°	4841.6
5°	4898.2
7.5°	4986.8
10°	5118.0
12.5°	5323.5
15°	5589.4
17.5°	5755.9
20°	5639.0
22.5°	5188.9
25°	4462.3
27.5°	3661.3
30°	2987.9
32.5°	2442.0
35°	1928.1
37.5°	1421.3
40°	939.2
42.5°	506.8
45°	304.9
47.5°	191.4
50°	124.1
52.5°	74.4
55°	35.5
57.5°	21.3
60°	17.7
62.5°	14.2
65°	10.6
67.5°	7.1
70°	7.1
72.5°	3.5
75°	3.5
77.5°	3.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)