

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583308

Luminaire Tested: **HC607D010-HM60525830-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583308
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC607D010-HM60525830-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 934.7 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583308

CATALOG NUMBER: HC607D010-HM60525830-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P583308

CATALOG NUMBER: HC607D010-HM60525830-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	93		104	99	95	92		96	92	90		93	90	88		90	88	86
3	100	93	87	83		98	91	86	82		89	84	81		86	83	80		84	81	78
4	94	86	79	75		92	85	79	74		82	77	73		80	76	72		78	75	72
5	89	79	73	68		87	78	72	68		76	71	67		75	70	66		73	69	66
6	83	73	67	62		82	73	66	62		71	65	61		70	65	61		68	64	60
7	79	68	62	57		77	68	61	57		66	60	56		65	60	56		64	59	56
8	74	64	57	52		73	63	57	52		62	56	52		61	56	52		60	55	51
9	70	59	53	48		69	59	53	48		58	52	48		57	52	48		56	51	48
10	66	56	49	45		65	55	49	45		54	49	45		53	48	45		53	48	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36603
5°	36848
10°	37274
15°	38037
20°	38252
25°	37055
30°	33625
35°	27331
40°	18148
45°	10102
50°	5663
55°	3144
60°	1743
65°	1310
70°	914
75°	678
80°	379
85°	440



TEST NUMBER: P583308

CATALOG NUMBER: HC607D010-HM60525830-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.9	6.8
10°-20°	189.0	20.2
20°-30°	278.5	29.8
30°-40°	249.1	26.7
40°-50°	108.1	11.6
50°-60°	31.8	3.4
60°-70°	10.2	1.1
70°-80°	3.6	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	531.4	56.9
0°-40°	780.6	83.5
0°-60°	920.4	98.5
0°-90°	934.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	934.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	668	
5°	670	64
15°	670	189
25°	613	279
35°	408	249
45°	130	108
55°	33	32
65°	10	10
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P583308

CATALOG NUMBER: HC607D010-HM60525830-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	667.7
2.5°	665.8
5°	669.6
7.5°	670.8
10°	669.6
12.5°	669.6
15°	670.2
17.5°	666.4
20°	655.7
22.5°	637.3
25°	612.6
27.5°	577.9
30°	531.2
32.5°	475.5
35°	408.4
37.5°	332.0
40°	253.6
42.5°	185.2
45°	130.3
47.5°	92.9
50°	66.4
52.5°	47.5
55°	32.9
57.5°	22.1
60°	15.9
62.5°	12.7
65°	10.1
67.5°	7.6
70°	5.7
72.5°	4.4
75°	3.2
77.5°	2.5
80°	1.2
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)